

MCS-IEC_NA

Mild steel combinable version, single door enclosure



HOFFMAN

CONNECT AND PROTECT



The mild steel single door combinable floor standing enclosure range, MCS, with a IP 55 protection degree, is available off the shelf in many different sizes. This enclosure range is well suited for many different applications. The risk for component failure, and with that unnecessary downtime, is eliminated as water and dust are prevented from entering the enclosure.

MATERIAL:

Frame: 1.5 mm painted steel. Door: 2 mm painted steel. Rear, roof and side panels: 1.5 mm painted steel. Mounting plate: 3 mm galvanized steel. Bottom plates: 1 mm galvanized steel.

FRAME:

Seam welded reversed open profiles with 25 mm hole pattern, according to DIN 43660. Including integrated external hole pattern.

DOOR:

Mounted with four hinges allowing left or right hand opening. Including door frame with 25 mm hole pattern.

REAR PANEL:

Fitted by M6 torx screws. Standard facilities for rear door mounting.

SIDE PANELS:

Supplied as an accessory.

ROOF PANEL:

Removable.

LOCK:

Espagnolette 4-point locking system. Does not interfere with the enclosure inner space. Standard double-bit lock with 3 mm insert. Standard inserts, cylinders, lift handles and T-handles are available as accessories.

BOTTOM PLATES:

Consists of three or four (D>600) pieces.

MOUNTING PLATE:

Double folded and slides into position. Adjustable in depth by steps of 25 mm, with the MPD02 accessory. Supplied, attached on the outside of the enclosure packaging.

EARTHING:

All panels are earthed through their fittings and are equipped with a separate earthing stud.

FINISH:

RAL 7035 structured powder coating.

PROTECTION:

Complies with IP 55 | TYPE 12 | IK 10.

MOUNTING REQUIREMENTS:



Standard delivery ready for combined installation. For stand-alone installation add side panels.

DELIVERY:

Frame with fitted door, rear panel, roof panel, bottom plates, mounting plate (not included for PER5 version) and door frame. For 400 mm wide enclosures, a mounting plate, bottom plates and door frame are not included. For enclosures 2200 mm height, delivery includes two CMB profiles mounted in depth. Delivery also includes earthing bolts. Delivered on a pallet which is identical to the width of the enclosure to allow baying without removal. All packing material is recyclable.

IP 55 | TYPE 12 | IK 10





CABLE ENCLOSURES: WITHOUT MP, BOTTOM PLATES AND DOOR FRAME

Enclosure dimensions			
H	W	D	Item no.
1800	400	400	MCS18044R5
1800	400	500	MCS18045R5
1800	400	600	MCS18046R5
2000	400	400	MCS20044R5
2000	400	500	MCS20045R5
2000	400	600	MCS20046R5
2000	400	800	MCS20048R5

WITH MOUNTING PLATE

Enclosure dimensions			Mounting plate dimensions		Usable depth	Item no.
H	W	D	h	w	d	
1400	600	500	1294	494	459	MCS14065R5
1400	800	500	1294	694	459	MCS14085R5
1600	600	500	1494	494	459	MCS16065R5
1600	800	500	1494	694	459	MCS16085R5
1800	500	500	1694	394	459	MCS18055R5
1800	600	400	1694	494	359	MCS18064R5
1800	600	500	1694	494	459	MCS18065R5
1800	600	600	1694	494	559	MCS18066R5
1800	600	800	1694	494	759	MCS18068R5
1800	800	400	1694	694	359	MCS18084R5
1800	800	500	1694	694	459	MCS18085R5
1800	800	600	1694	694	559	MCS18086R5
1800	800	800	1694	694	759	MCS18088R5
1800	1000	400	1694	894	359	MCS18104R5
1800	1000	500	1694	894	459	MCS18105R5
1800	1000	600	1694	894	559	MCS18106R5
1800	1000	800	1694	894	759	MCS18108R5
2000	500	500	1894	394	459	MCS20055R5
2000	600	400	1894	494	359	MCS20064R5
2000	600	500	1894	494	459	MCS20065R5
2000	600	600	1894	494	559	MCS20066R5
2000	600	800	1894	494	759	MCS20068R5
2000	800	400	1894	694	359	MCS20084R5
2000	800	500	1894	694	459	MCS20085R5
2000	800	600	1894	694	559	MCS20086R5
2000	800	800	1894	694	759	MCS20088R5
2000	1000	400	1894	894	359	MCS20104R5
2000	1000	500	1894	894	459	MCS20105R5
2000	1000	600	1894	894	559	MCS20106R5
2000	1000	800	1894	894	759	MCS20108R5
2200	600	600	2094	494	559	MCS22066R5
2200	600	800	2094	494	759	MCS22068R5
2200	800	600	2094	694	559	MCS22086R5
2200	800	800	2094	694	759	MCS22088R5
2200	1000	600	2094	894	559	MCS22106R5
2200	1000	800	2094	894	759	MCS22108R5