

CCY10L18LT38G Covered Rope Lay Braid

By Burndy

Catalog # [CCY10L18LT38G](#)

Covered Rope Lay Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance CM
Status
Certification - CSA Approved No

Configuration

Connector Type Rope lay

Dimensions

Dimension - L Length Overall 471.93 mm
mm
Length 18 in
Dimension - Length Overall 18.58 in
inch

General

UPC 12 Digit 781810674567
UPC 14 Digit GTIN 00781810674567
Material Copper
UPC 781810674567

Logistics

Minimum Pack Quantity 1
Carton Quantity 50
Pallet Quantity 4800

Product Assets

[Catalog \[English\]](#)