

GAR1726W, Mechanical Grounding Connector, Cable to Rod or Pipe, Tin Plated

By Burndy

Catalog # [GAR1726W](#)



To Rod or Pipe with the Same Connector; Hot Tin Dipped.

Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

General

Catalog Number	GAR1726W
Installation Torque	240 Lb in
Recommended Run in-lb	
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
U Bolt Type	268
UPC	781810117057
UPC 14 Digit GTIN	00781810117057

Dimensions

Dimension - Height inch	4.00 in
Dimension - Height mm	101.6 mm
Dimension - Outside Diameter inch	1.90 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	1 1/2

Conductor - Copper Tube Std Size Range	1 1/2
Conductor - Pipe or Round Tube Size Range	1-1/2 in
Conductor - Rod Size	1.620-1.90 in
Conductor - Rod Size Range	1 5/8-1 7/8
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	30
Minimum Pack Quantity	16

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_GAR_Lineart](#)
- [Sales Drawings - SD015789](#)
- [Specifications - GAR1726W](#)