

# GAR1826W, Mechanical Grounding Connector, Cable to Rod or Pipe, Tin Plated

By Burndy  
Catalog # [GAR1826W](#)



Ground Clamp Copper Tin Plated bodies and electro tin plated hardware 4 AWG-2/0 AWG Installation Torque Recommended Run in-lb240 LB in.

## Features

- Parallel or 90° Copper Cable Connection
- One-wrench installation
- Rated for Direct Burial in earth or concrete

## General

Catalog Number	GAR1826W
Installation Torque	240 Lb-in
Recommended Run in-lb	
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
U Bolt Type	257
UPC	781810001486
UPC 14 Digit GTIN	00781810001486

## Dimensions

Dimension - Height inch	4.25 in
Dimension - Height mm	108 mm
Dimension - Outside Diameter inch	2.38 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

## Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Tube Std Size	2

Conductor - Copper Tube Std Size Range	2
Conductor - Pipe or Round Tube Size Range	2 in
Conductor - Rod Size	2 in-2.38 in
Conductor - Rod Size Range	2-2 1/4
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> <li>• CU Tube Std-Size</li> <li>• Rod-Size</li> </ul>

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	6
Minimum Pack Quantity	14

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_GAR\\_Lineart](#)
- [Sales Drawings - SD..015789-01](#)
- [Specifications - GAR1826W](#)