

QO1515

QO Tandem Mini CB 15 A 1P 120/240 V 10 kA Plug-in Mount

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Miniature circuit-breaker
Range of product	QO
Line Rated Current	15 A
System Voltage	120/240 V AC
Mounting mode	Plug-in
Poles description	1P
Circuit breaker type	Tandem
Circuit breaker application	HACR rated
Electrical connection	Box lugs

Complementary

Breaking capacity	10 kA at: 120/240 V AC
Number of spaces required	1
AWG gauge	AWG 14...AWG 8 (copper or aluminium)
Height	3.22 in
Depth	2.91 in
Width	0.75 in

Environment

Product certifications	CSA UL listed
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	00181 - REPLCMNT TANDEMS - DO NOT NEGOTIATE
----------	---

Discount Schedule	DE2A
GTIN	00785901400905
Nbr. of units in pkg.	10
Package weight(Lbs)	0.32000000000000001
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------