

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Miniature circuit-breaker
Range of product	QO
Line Rated Current	20 A
System Voltage	120 V AC
Mounting mode	Plug-in
Poles description	1P
Circuit breaker type	Ground fault protecting class A 6 mA
Circuit breaker application	Not rated
Electrical connection	Pressure plate

### Complementary

Breaking capacity	10 kA at: 120 V AC
Number of spaces required	1
AWG gauge	AWG 14...AWG 8 (copper) AWG 12...AWG 8 (aluminium)
Height	4.12 in
Depth	2.91 in
Width	0.75 in

### Environment

Product certifications	CSA UL listed
Ambient air temperature for operation	104 °F (40 °C)

### Ordering and shipping details

Category	00003 - QO 1&2 POLE GFI CB 30A MAX
Discount Schedule	DE2A

GTIN	00785901255079
Nbr. of units in pkg.	1
Package weight(Lbs)	0.530000000000000003
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1340 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------