



Project / Job Name: _____

Location: _____

Fixture Type: _____

Notes: _____

65-1211 - LED 4 Foot Wrap; 39 Watts;
27K/30K/35K/40K/50K CCT Selectable; White Finish;
120-277 Volt



GENERAL

| | |
|---------------------------|-----------------------------------|
| Company | NUVO |
| EA Height | 47.64 |
| EA Width | 2.76 |
| EA Length | 5.71 |
| Bulb Included | Integrated |
| Material | Steel |
| Fixture Type | Ceiling Wrap |
| Status | Active |
| Style | Utility |
| Surge Protection | Built-in surge protection - 2.5KV |
| Total Harmonic Distortion | <20% |
| CCT Selectable | Yes |
| Wattage Selectable | No |
| Finish Family | White |
| Amps | 0.330A |
| Has Camera | No |
| IOT Enabled | No |
| Lens Finish | White |
| Lens Material | Polycarbonate (PC) |
| Lensed | Yes |
| Power Factor | 0.9 |
| SDS Class | LED Fixture |
| Indoor Outdoor | Indoor |
| Product Technology | LED |
| Incandescent Equivalent | 175W |

ELECTRICAL

| | |
|---------------------|-------------------------------|
| CCT (Kelvin Temp) | 2700K/3000K/3500K/4000K/5000K |
| Dimmable | Non-Dimmable |
| Hours Rated | 50000 |
| Beam Angle (degree) | 110 |
| Color Temp | Warm White to Natural Light |
| CRI | 90+ |
| Operating Frequency | 50/60Hz |
| Operating Temp | -20C (-4F) to +40C (+104F) |
| Lumens | 3200L-3400L |
| Volts | 120V-277V |
| Watts | 39W |

PHYSICAL

| | |
|---------------|----------------|
| Lamp Base | Integrated |
| Finish | WHITE |
| ANSI Base | Integrated |
| Lamp Type | Integrated LED |
| Fixture Shape | Linear |

ADDITIONAL INFO

| | |
|----------|---------|
| Warranty | 5-Years |
|----------|---------|

PACKAGING

| | |
|---------------|----------------|
| UPC | 045923656644 |
| Case Cube | 2.0767 |
| Case Height | 6.3 |
| Case Length | 48.23 |
| Case Quantity | 4 |
| Case UPC | 10045923656641 |
| Case Weight | 19.87 |
| Case Width | 11.81 |
| EA Cube | 0.4345 |
| EA Height | 47.64 |
| EA Length | 5.71 |
| EA Quantity | 1 |
| EA Weight | 4.46 |
| EA Width | 2.76 |
| Inner Cube | 0.0 |
| Pack Type | Box |
| Web Height | 2.56 |
| Web Length | 47.24 |
| Web Width | 5.5 |

COMPLIANCE

| | |
|-----------------|---|
| ADA Compliant | Yes |
| CA Prop 65 | Lead |
| FCC Compliant | Yes |
| Location Rating | Damp |
| NEC Compliance | Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5) |
| ROHS Compliant | Yes |
| Safety Listing | cETLus |
| California Ban | Lawful for sale |
| Title 20 | Exempt |
| T24 Compliant | No |