








This item includes:

 Item No.: 221-412 Splicing connector with levers; for all conductor types; max. 4 mm ² ; 2-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm ² ; transparent	 Item No.: 221-413 Splicing connector with levers; for all conductor types; max. 4 mm ² ; 3-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm ² ; transparent	 Item No.: 221-415 Splicing connector with levers; for all conductor types; max. 4 mm ² ; 5-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm ² ; transparent	 Item No.: 221-500 1 Mounting carrier; 221 Series - 4 mm ² ; for DIN-35 rail mounting/screw mounting; orange
 Item No.: 221-612 Splicing connector with levers; for all conductor types; max. 6 mm ² ; 2-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 6,00 mm ² ; transparent	 Item No.: 221-613 Splicing connector with levers; for all conductor types; max. 6 mm ² ; 3-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 6,00 mm ² ; transparent	 Item No.: 221-615 15 Splicing connector with levers; for all conductor types; max. 6 mm ² ; 5-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 6,00 mm ² ; transparent	

Notes

General safety information

NOTICE: Observe installation and safety instructions!

- **Only to be used by electricians!**
- Do not work under voltage/load!
- Use only for proper use!
- Observe national regulations/standards/guidelines!
- Observe technical specifications for the products!
- Observe the number of permissible potentials!
- Do not use damaged/dirty components!
- Observe conductor types, cross-sections and strip lengths!
- Insert conductor until it hits the product's backstop!
- Use original accessories!

To be sold only with installation instructions!

Physical data

Width	259 mm / 10.197 inches
Height	63 mm / 2.48 inches
Depth	155 mm / 6.102 inches

Material data

Note (material data)	Information on material specifications can be found here
Fire load	12.23 MJ
Weight	1015.5 g

Commercial data

PU (SPU)	1 pcs
Packaging type	Box
Country of origin	CN
GTIN	4055143739160
Customs tariff number	85369010000

Product Classification

UNSPSC	39121409
eCl@ss 10.0	27-14-11-04
eCl@ss 9.0	27-14-11-04
ETIM 9.0	EC000446
ETIM 10.0	EC000524
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product
Compliance 887-957

