

Specifications



Eaton TRGF20W

Eaton tamper-resistant, self-test GFCI, 20A, 125V, White, Slim design

General specifications

PRODUCT NAME	Eaton slim GFCI receptacle
---------------------	----------------------------

CATALOG NUMBER	TRGF20W
-----------------------	---------

PRODUCT LENGTH/DEPTH	1.03 in
-----------------------------	---------

PRODUCT HEIGHT	4.19 in
-----------------------	---------

PRODUCT WIDTH	1.69 in
----------------------	---------

PRODUCT WEIGHT	3.9 lb
-----------------------	--------

WARRANTY	Refer to warranty document.
-----------------	-----------------------------

CERTIFICATIONS	cULus Listed NOM
-----------------------	---------------------

PRODUCT TYPE	Slim GFCI receptacle
---------------------	----------------------



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Slim design
TYPE	Self-test
AMPERAGE RATING	20A
VOLTAGE RATING	125V
CIRCUIT INTERRUPTER TYPE	GFCI
PACKAGING TYPE	Bulk packaging
FEATURES	Tamper resistant FedSpec Certified
WIRING METHOD	Back and side wire
ALLOWABLE WIRE SIZE	#14-10 AWG
NEMA CONFIGURATION	5-20R
TORQUE RATING	16 lbf-in
COLOR	White

Resources

SPECIFICATIONS AND DATASHEETS

[Tamper and weather resistant slim GFCI receptacles spec sheet](#)

[GFCI Cross Reference](#)

[Standard slim GFCI spec sheet](#)

[Tamper resistant slim GFCI receptacles spec sheet](#)

[Controlled slim GFCI spec sheet](#)

[Arrow Hart tamper resistant slim GFCI spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

