

PLATED CARRIAGE BOLTS BOULONS DE CARROSSE PLAQUÉS

129
Series

Used extensively for Truck Rack and Floorboard construction or repair. Fully threaded for proper fit and adjustment in wood.



ORDER BY STOCK NUMBER

Length Overall	Bolt Diameter							
	1/4	Std. Pkg.	5/16	Std. Pkg.	3/8	Std. Pkg.	1/2	Std. Pkg.
3/4	129-307	100	129-442	100	129-487	100	-	-
1	129-309	100	129-444	100	129-489	100	129-579	50
1-1/4	129-311	100	129-446	100	129-491	100	129-581	50
1-1/2	129-313	100	129-448	100	129-493	100	129-583	50
2	129-316	100	129-451	100	129-496	100	129-586	50
2-1/2	129-318	100	129-453	100	129-498	100	129-588	50
3	129-320	100	129-455	100	129-500	100	129-590	50
3-1/2	129-322	100	129-457	100	129-502	100	129-592	50
4	129-324	100	129-459	100	129-504	100	129-594	50
4-1/2	129-325	100	129-460	100	129-505	100	129-595	50
5	129-326	100	129-461	100	129-506	50	129-596	25
6	129-329	100	129-464	50	129-509	50	129-599	25
8	-	-	-	-	129-513	50	129-603	25
10	-	-	-	-	129-517	10	129-607	10
12	-	-	-	-	129-520	10	129-610	10

Note: Plated Grade 5 Carriage Bolts are available. See current price list Industrial Price Book. Full shank Carriage Bolts available upon request.

PLATED CARRIAGE BOLTS BOULONS DE CARROSSE PLAQUÉS

129
Series

UTILITY ASSORTMENT

No. 020-330

- This Assortment contains 70 Plated Bolts and Nuts, 14 sizes.
- Each size in a compartment in a sturdy fibre-board container with retail prices shown.
- Particularly useful for farm, garage and general repair work.



PLATED GRADE 5 PLOW BOLTS BOULONS DE CHARRUE CLASSE 5 PLAQUÉS

133
Series

- Regular No. 3 Head
- High Carbon Steel
- Double Heat Treated

Papco® Plow Bolt heads are round and countersunk with a square neck. Oversize heads for 3/8" Dia. are 7/16" Dia. head and 7/16" Dia. is 1/2" Dia. head. Length is measured overall from end of bolt to the top of the head. Other heads and styles are available.



ORDER BY STOCK NUMBER

Standard Package: 3/8" Dia. 100; 7/16" and 1/2" Dia. 50; 5/8" Dia. 25

Length Overall	Standard Head				Oversize Head		Length Overall	Standard Head				Oversize Head	
	3/8	7/16	1/2	5/8	3/8	7/16		3/8	7/16	1/2	5/8	3/8	7/16
1	133-489	133-534	-	-	-	-	2	133-496	133-541	133-586	133-675	-	133-820
1-1/4	133-491	133-536	133-581	-	133-791	-	2-1/4	-	-	-	133-676	-	133-822
1-1/2	133-493	133-538	133-583	133-672	133-793	-	2-1/2	133-498	133-543	133-588	133-677	-	133-824
1-3/4	133-495	133-540	133-585	133-674	-	133-816	3	-	133-545	133-590	133-679	-	-

PLATED LAG BOLTS TIRE-FONDS PLAQUÉS

135
Series

- Hex Head
- Sharp Gimlet Point



ORDER BY STOCK NUMBER

Standard Package: 100, *50, **25

Dia. Length		1/4	5/16	3/8	1/2	Dia. Length		1/4	5/16	3/8	1/2
1	135-309	135-444	-	-	-	4	135-324	135-459	135-504	135-594*	
1-1/4	135-311	135-446	-	-	-	4-1/2	135-325	135-460	135-505	135-595*	
1-1/2	135-313	135-448	135-493	-	-	5	135-326	135-461	135-506*	135-596*	
2	135-316	135-451	135-496	135-586*	-	6	135-329	135-464	135-509*	135-599**	
2-1/2	135-318	135-453	135-498	135-588*	-	7	-	-	135-511*	135-601**	
3	135-320	135-455	135-500	135-590*	-	8	-	-	135-513*	135-603**	
3-1/2	135-322	135-457	135-502	135-592*	-						

Length of Lag Bolt is measured from under head to end of point. Thread is one-half of length plus 1/2". Larger and longer sizes are available.