



YAV3/OT12B, Compression Terminal, 1-Hole, 3/0 Flex, 1/2" Stud, Short Barrel, Belled End, Tin Plated

By Burndy
Catalog # [YAV3/OT12B](#)

Copper Compression Terminal

Application

Wire Termination

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor - Material	Copper
Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Terminal

Current

Voltage - Maximum	35000
Voltage Rating	35 kV

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.74 in



Dimension - Outside Diameter inch	0.69 in
Dimension - Z inch	0.57 in
Dimension - L Length Overall mm	56 mm
Dimension - Pad Width inch	1.02 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Length Overall inch	2.22 in
Dimension - Thread Size	1/2
Dimension - N inch	0.53 in

General

Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Belled
Type	Standard Belled Barrel, Tin Plated
UPC 12 Digit	781810425633
UPC 14 Digit GTIN	00781810425633
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC	781810425633

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)