

# Waterproof Power Box

LUM-D01



## Key Features

- For Select P55, P54, and P45 PTZs
- Aluminum Alloy and SECC Construction
- Dimensions: 297.2 mm x 248.0 mm x 130.7 mm (11.7 in. x 9.8 in. x 4.1 in.)
- Max. Load Capacity: 8.0 kg (17.6 lb)
- Compatible With Wall, Corner, and Pole Mounts
- IP66 Rating

## Learn More



View the accessory selector for all mount options.

## Specifications

Weight	3.4 kg (7.5 lb)
Load Bearing Capacity	8.0 kg (17.6 lb)
Material	Aluminum Alloy and SECC
Color	White
Dimensions	297.2 mm x 248.0 mm x 130.7 mm (11.7 in. x 9.8 in. x 4.1 in.)
Thread Size	G½ in.
IP Rating	IP66
Operating Temperature	-40 °C to 60 °C (-40 °F to +140 °F) < 90% (RH)
Storage Temperature	-40 °C to 60 °C (-40 °F to +140 °F) 10% to 90% (RH)

## Dimensional Drawing

mm [in.]

