



7-in-1 Hammer Facing Insulated Lineman Wrench



The Klein Tools 7-in-1 Hammer Facing Insulated Lineman Wrench combines six common wrench sizes with dual integrated hammer faces for maximum versatility. The machined, double-sided striking faces enable linemen to work faster without rotating the tool, thereby reducing drop risk and increasing efficiency while working. Built with 1000V Rated, 3-Layer insulation featuring a white warning layer for wear indication, this wrench provides trusted protection in energized environments.

Specifications

Type:	Lineman Wrench	Application:	Utility
Special Features:	7-in-1 Dual Hammer Facing; Insulated	Head Type:	Forged
End Type:	Ratcheting Square/Hex	Reversible:	Yes
Material:	Steel	Finish:	Black Phosphate
Size:	Socket Sizes: 3/4", 13/16", 1", 1-1/8"; Hex Sizes: 9/16", 3/4"	Swing Arc:	11.25°
Offset Angle:	0°	Number of Points:	4; 12
Number of Teeth:	32	Overall Length (Inch):	2.37
Overall Length (cm):	6	Overall Height (Inch):	1.8
Overall Height (cm):	4.6	Overall Width (Inch):	11.36
Overall Width (cm):	28.9	Weight (oz):	30.4
Weight (g):	862		