

FEATURES & SPECIFICATIONS

INTENDED USE — Recessed housing rated IC or Non-IC. For new construction only.

Approved for all ceiling and wiring types.

Approved for direct burial in insulation.

CONSTRUCTION — Air-tight standard. Tested to meet current energy codes.

Aluminum foam-gasketed housing with galvanized steel pan.

Galvanized bar hangers span up to 24" o.c. and feature stepped shank nail and positioning guide with integral T-bar locks. Two locking screws hold fixture in position.

Galvanized steel junction box with four built-in Romex clamps. Four 1/2" and two 3/4" knockouts with slots for pryout. Rated for through branch wiring.

Maximum 4 (2 in, 2 out) No. 12 AWG conductors. Rated for 90°C.

Ground wire provided.

Removable J-box doors for easy access.

ELECTRICAL — Quick disconnect provided for power connection to the LED modules.

Paint overspray masked by disposable disconnect plug.

Housing and LED module combination is IC rated and thermally protected.

120 volt only.

INSTALLATION — Air-tight housing suitable for air-tight installations. Refer to energy codes for proper installations.

2x8 and 2x6 wood joist or T-bar installation.

Expandable bar hangers allow for off-center mounting in wood joist or T-bar ceilings. Length of 25-1/2" maximum 13-1/4" minimum or cut to fit 5-1/2" on center joist construction.

Vertical adjustment of housing allows for flush mounting with ceiling face.

Suitable for ceilings up to 1-1/2" thick.

LISTINGS — UL Listed to US and Canadian safety standards. Damp location listing (See trim selection for wet location listing).

WARRANTY — 1-year limited warranty. Complete warranty terms located at <u>www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx</u>

Note: Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

Catalog Number


Notes


Туре

4" LED Housing

L3LED T24







Height: 5-1/4 (13.3) Length: 13-1/4 (33.7) Width: 12-3/16 (30.9) Ceiling opening: 4 (10.2)

All dimensions are inches (centimeters) unless otherwise specified.

ORDERING INFORMATION For shortest lead times, configure product using bolded options.			Example: L3LED T24
L3LED T24			
Series	Options	Packaging	
L3LED T24	Shipped installed in fixture PHC Poke-home wire connector	R6 Resale pack of six U Unit	

Accessories: Order as separate catalog number.

ATK3 R6 Airtight trim kit

Notes See trim summary on reverse side for maximum wattages.

P Series Open and Baffle Wide Flange LED Modules (Wet Location)







Series/Finish		Lamp	CCT / CRI / W	/ Lumens ¹	Voltage
4BPMW	4" Baffle LED module, matte white	LED	(blank)	3000 K / 83CRI / 10.6W / 620L	(blank) 120V
4BP TRMW	4" Baffle LED module, black baffle, matte white flange		27K 90CRI	2700 K / 93CRI / 11.2W / 600L	
4BPBN	4" Baffle LED module, brushed nickel		30K 90CRI	3000 K / 93CRI / 11.2W / 600L	
4BPORB	4" Baffle LED module, oil-rubbed bronze		40K 90CRI	4000 K / 92CRI / 9.9W / 650L	
40PA	4" Open LED module, clear diffuse				
40PAZ	4" Open LED `module, clear specular				
40PA TRMW	4" Open LED module, clear diffuse, matte white flange				
40PAZ TRMW	4" Open LED module, clear specular, matte white flange				

Notes

1 Total system delivered lumens.

LED Gimbal Module (Damp location)



ORDERING INFORMATION	Example: 4G1MW LED L3LED T24			
4G1		LED		
Series/Finish		Lamps	CCT / CRI / W / Lumens ²	Voltage
Series 4G1 4" Gimbal module	Finish MW Matte white MB Matte black ¹ BN Brush nickel ¹ ORB Oil-rubbed bronze ¹	LED	(blank) 3000k / 83CRI / 7.9W / 435L 27K 90CRI 2700K / 91CRI / 8.3W / 480L 30K 90CRI 3000K / 93CRI / 7.7W / 500L 40K 90CRI 4000K / 94CRI / 8W / 560L	(blank) 120V

Notes

Available in 30K 83CRI only.
 Total system delivered lumens.

2 Total system delivered lumens.

E Series Baffle Wide Flange LED Modules (Wet Location)



ORDERING INFORMATION For shortest lead t	Example: 4BEMW L3LED T24			
4BEMW		LED		
Series/Finish		Lamps	CCT / CRI / W / Lumens ¹	Voltage
Series 4BEMW 4" Baffle LED module, matte white	Finish MW Matte white MB Matte black BN Brush nickel ORB Oil-rubbed bronze	LED	27K 2700 K /82CRI/10.3W/530L 30K 3000 K /82CRI/10.3W/570L 40K 4000 K /82CRI/10.3W/600L	(blank) 120V

Notes 1 Total system delivered lumens.



L3LED-T24