




Data Sheet | Item Number: 750-965

Fieldbus Connector CC-Link; with D-sub male connector; 9-pole

<https://www.wago.com/750-965>



Color: ■ light gray



Dimensions in mm

This fieldbus connector links a CC-Link device to a CC-Link line.

The fieldbus connector has the following features:

- Two horizontal cable entries for both input and output
- Fast and maintenance-free CAGE CLAMP® connection – a locking slide keeps the clamping unit in its open position
- Externally operable switch to activate or deactivate the network terminating resistor

For the first and last station on the bus, the switch must be set to "ON" (Terminating resistor activated)

Switch setting to "OFF" for downstream bus stations (Terminating resistor deactivated)



Technical data	
Connection type	D-sub 9 plug
Pole number	9
Communication/fieldbus	CC-Link
Transmission rate	-

Connection Data	
Connection type	CAGE CLAMP® terminal strip with locking slide (218 Series)
Solid conductor	0.08 ... 0.5 mm² / 28 ... 20 AWG
Strip length	5 ... 6 mm / 0.2 ... 0.24 inches

Physical data	
Width	45 mm / 1.772 inches
Height	16 mm / 0.63 inches
Depth	54 mm / 2.126 inches

Mechanical data	
Connectable sheathed cable diameter	4.5 ... 9.5 mm
Cable glands (number)	2
Housing material	PA66-105-V2
Weight	34.1 g

Environmental requirements	
Ambient temperature (operation)	0 ... +60 °C
Ambient temperature (storage)	-25 ... +85 °C
Protection type	IP20
Relative humidity (without condensation)	95 %
Fire load	0.26 MJ

Commercial data	
Product Group	15 (I/O System)
PU (SPU)	1 pcs
Packaging type	Bag
Country of origin	DE
GTIN	4050821096030
Customs tariff number	85366990990

Product Classification	
UNSPSC	39121421
eCl@ss 10.0	27-24-26-92
eCl@ss 9.0	27-24-26-92
ETIM 9.0	EC002584
ETIM 10.0	EC002584
ECCN	NO US CLASSIFICATION



Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 508	E175199

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 750-965	

Documentation

Bid Text			
750-965	06.10.2017	doc 24.50 KB	
750-965	19.02.2019	xml 4.43 KB	

CAD/CAE-Data

CAE data	
EPLAN Data Portal 750-965	