


Duct tapes from IDEAL Electrical are built to support all your bundling, repair, and sealing needs. Designed for strong adhesion and durable performance, our duct tape lineup features both general-purpose and heavy-duty options. Whether you're working in an industrial environment or tackling a DIY project, IDEAL offers the right tape for the job.



		46-2929 General Purpose, Gray	46-3939 Heavy-Duty, Blue
Description		High-adhesion duct tape for the everyday needs of contractors and DIYers alike	Premium-grade, durable duct tape built for the most demanding industrial conditions
Features		Grips instantly and holds strong on a variety of surfaces. Hand-tearable with a polyethylene backing that resists scuffs and damage	27% thicker polyethylene backing for enhanced durability and resistance to UV and moisture Distinctive blue color stands out in industrial settings
Backing		Polyethylene Coated Cloth	
Overall Thickness		8.6 mils	11 mils
Adhesive Type		Natural Rubber Based Adhesive Backing	
Tensile Strength		18kg / 25mm	
Service Temperature		0°C - 93°C [32°F - 200°F]	
Shelf Life		1 year from date of manufacture	
Color		Silver / Gray	IDEAL Blue
Prop65		Product meets CA Prop. 65 requirements	
Tape Dimensions		1.88" X 60 Yards [48mm X 54.8m]	
Approx. Roll Diameter		5-7/8 in. (149.2 mm)	6.5 in. (165 mm)
Quantity (Master Pack)		24	
Optimal Storage		Ambient 25°C with 50 - 65% R.H. (Relative Humidity)	
Peel Adhesion		1.0kg / 25mm	0.75kg / 25mm
Tack Ball Test		#13 Ball < 20 cm	#20 Ball < 20 cm
Applicable Temperature		41°F-95°F [5°-35°C]	

The above mentioned data represent the average obtained in a laboratory environment. Suggestion for use and final results are based on our best technical experiences but cannot be intended as our commitment or liability. The user will determine the suitability of the product and the method of application for each specific use.