



300-Foot Open Reel Tape Measure with Single Hook and Carabiner



Klein Tools 94300RT 300-Foot Open Reel Tape Measure combines extended reach with precision engineering for professionals tackling large-scale projects. The PVC-coated fiberglass tape provides superior durability and significantly reduces stretch. The carabiner and hook both share the same zero point, while an efficient 3:1 planetary gear system operates smoothly while enabling faster blade retraction to save time on large job sites.

Specifications

Type:	Open Reel Tape Measure	Application:	Linear Measurement
Special Features:	SS Stake Stored in Handle, Hook with Carabiner, Disengaging Hand Crank	Material:	ABS, TPR
Tape Length:	300"	Tape Width:	1/2" (1.27 cm)
Tape Material:	Fiberglass	Tape Coating:	PVC
Measurement Standard:	Imperial (SAE), Engineer's Scale	Graduations:	1/10"
Lockable Tape:	No	Rewind Type:	Manual
Hook:	Single	Magnetic:	No
Belt Clip:	No	Case Material:	ABS, TPR
Case Color:	Orange, Black	Overall Width (Inch):	10.13
Overall Width (cm):	25.7	Overall Height (Inch):	14.03
Overall Height (cm):	35.6	Overall Length (Inch):	2.18
Overall Length (cm):	5.5	Weight (oz):	60.32
Weight (g):	1710		