



GUELPH, ONT. BARABOO, WI. COMPTON, CA. MONTERREY, MX



HPS UNIVERSAL™
DRY TYPE ISOLATION/BUCK-BOOST TRANSFORMER

HV/HT	120X240V
BIL	-
TERM. BORNES	H1 H3 H2 H4
LV/BT	12/24V
BIL	-
TERM. BORNES	X4 X2 X3 X1

Cust. Ref. Réf. du client	
Serial No. No. de série	
Part No. No. de pièce	QC35ERCB
PHASE	1
kVA	0.35
TYPE	Q
Cooling Refroidissement	ANC
Temp. Rise Échauffement	80 °C
Temp. Class Classe de Temp.	130 °C
Frequency Fréquence	50/60 Hz
Impédance % @ _____ °C	
Encl. Type Type de boîtier	3R
Wt Poids lbs/kg	18.1/8.2
Winding Enroulement	COPPER

This transformer can be wired as both an isolation transformer and buck-boost transformer. Refer to wiring instructions for details.

d001073bsrww1



MADE IN CANADA



TITLE: 1 PHASE ENCAPSULATED TRANSFORMER
 NAMEPLATE INFORMATION


4	26/04/28	LC	HCN: 85668	DES: WWONG
3	26/02/23	LC	CHANGED NPL VER:	DATE: 09/04/14
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 1 OF 2


EDB0C35ERCB

THIS DRAWING CONTAINS STRICTLY CONFIDENTIAL INFORMATION BELONGING TO HAMMOND POWER SOLUTIONS AND MUST NOT BE DISTRIBUTED OUTSIDE AUTHORIZED PARTIES. 4.2 httpd 2026/06/11 12:58

FRONT VIEW



SIDE VIEW



FRONT & BOTTOM PANEL IS HINGED FOR ACCESS TO TERMINALS, BOTTOM MOUNTING HOLES AND REAR KNOCKOUT.

All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

CUSTOMER NOTES:

- HV TERMINATED AT #18 AWG LEAD WIRE
- LV TERMINATED AT #14 AWG LEAD WIRE



TITLE: 1 PHASE ENCAPSULATED TRANSFORMER

4	26/04/28	LC	HCN: 85668	DES: WWONG
3	26/02/23	LC	CHANGED NPL VER:	DATE: 09/04/14
NO.	DATE	BY	REVISION	SCALE: NTS

SHEET 2 OF 2

EDB0C35ERCB