



Pass and Seymour  
800 Series Cable Reel with Tri-Tap, 40FT, 12AWG, 15A  
Part No. CR08123N40T15



Delivers simple, reliable power distribution with 40 feet of reach and clear illuminated NEMA 5-15 tri-tap connector, making it easy to support multiple connections and confirm power at a glance. Built with a durable, lightweight nonmetallic enclosure and a detachable rotating mounting bracket, it installs quickly and performs in everyday applications. Designed as a streamlined, single-SKU solution, the 800 Series Cable Reel reduces complexity while meeting core performance needs in data centers, education and light commercial spaces.

## Features & Benefits

Clear illuminated NEMA 5-15 triple tap  
12/3 SJTW yellow cord, 105C rated  
15A push button breaker in reel housing

Rugged nonmetallic enclosure  
2ft incoming cord with NEMA 5-15 plug  
Detachable rotating mounting bracket

## Specifications

### General Info

|                    |                |               |                          |
|--------------------|----------------|---------------|--------------------------|
| Product Line       | Pass & Seymour | Color         | Black                    |
| Country Of Origin  | China          | Features      | Illuminated, Retractable |
| Application Sector | Commercial     | Warranty Type | 1-Year                   |
| Type               | Cable Reel     |               |                          |

### Dimensions

|                   |         |                   |         |
|-------------------|---------|-------------------|---------|
| Product Depth US  | 6.0 in  | Product Height US | 15.5 in |
| Product Length US | 14.0 in |                   |         |

### Listing Agencies / 3rd Party Agencies

|            |     |
|------------|-----|
| ETL Listed | Yes |
|------------|-----|

### Additional Information

|                |    |
|----------------|----|
| Energy Savings | No |
|----------------|----|

Technical Information

|                       |           |                      |            |
|-----------------------|-----------|----------------------|------------|
| Wire Gauge            | 12 AWG    | Cord Length          | 40 ft      |
| Amperage              | 15 A      | Number of Conductors | 3          |
| Indoor/Outdoor        | Indoor    | Mobile End           | Triple Tap |
| Operating Temperature | -10°-40°C | Voltage              | 125.0 V    |