

HN 3R Side-Mount Filter Fans 230V IP55, 12.8x12.8x6.31, Black, Plastic



CATALOG NUMBER

HN1226513

HN 3R Side-Mount Filter Fans quickly install into enclosure with a click-fit design; no tools or screws required. Grilles open with the flick of a finger for easy filter replacement.

INDUSTRY STANDARDS

UL/cUL Listed; File No. E482010

CE, UK CA, UL

Type 12, 3R standard

IP55 standard on all models except HN04

FEATURES

Click-fit design quickly installs into enclosure wall; no tools or screws required

Grille opens with the flick of a finger for easy filter replacement

Enclosure side wall mounting

Reverse airflow option on items ending with "R" available to push/pull air through higher static pressure

Standard rope gasket provides proper seal to the enclosure

Similar cut-out sizes as other filter fan manufacturers

Terminal block connections

Optional thermostat available to save energy and extend service life

Hinged grille remains attached after opening

Size range from 4 in. (102 mm) to 12 in. (305 mm)

Service life hours from 40,000 to 98,000 hours

PRODUCT ATTRIBUTES

Article Number: 59955

Airflow: 235ft³/min

Nominal Voltage: 230V

Height: 12.8in

Width: 12.8in

Depth: 6.31in

Max Current: 0.35A

Operating Temperature: 14 – 131°F

Material: Plastic

Finish: Smooth Matte

Color: Black

Color Code: RAL 9005

Weight: 8.11lb

ADDITIONAL PRODUCT DETAILS

Unit depth is of the entire unit.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE