KVG-24060-DWJ

24V Constant Voltage 60W Driver 5-in-1 Dimmable



Project:

Location:

Qty:

Notes:

DESCRIPTION

24V 60W class 2 power supply with built-in wiring compartments for line and low voltage connections

5-in-1 forward and reverse phase dimming:

TRIAC / ELV / MLV, 0-10V, 1-10V, Potentiometer, 10V PWM

FEATURES & BENEFITS

120V - 277V AC input

Built-in power factor correction, PF > 0.98

Protections:

short circuit, over-voltage, over-heat, over-load


Multiple knock-outs for easy wiring


Minimum / Maximum Load: 6W / 60W

0.5 second start time


SPECIFICATION	
Applications	LED Tape, 24V Ceiling Fixtures
Power	60 W
Input	120V - 277V AC
Output V / A	24V DC / 2.5A
Dimmability	TRIAC, 0-10V, 1-10V, Pot., 10V PWM
Approved Location	Dry, Damp & Wet Locations
Wiring Volume	5 cu in per chamber
Ambient Temperature	-40°F (-40°C) to +140°F (+60°C)
Warranty	5 Year
Certification	c UL us, FCC

WIRING DIAGRAMS





Derating Curve - load accordigly



ORDERING GUIDE **KVG-24060-DWJ**

COMPLIANCE

Class 2, Type HL, FCC

WARNING:

Do not exceed ambient temperature range from -40°F (-40°C) to +140°F (+60°C). Please mount in a shaded area or when mounted indoors

install in a well-ventilated area. Failure to follow these instructions could lead to overheating, short life and void the warranty.

Lotus LED Lights USA	www.LotusLEDLights.com	**Lotus LED Lights CANADA**
250 H Street # 301, Blaine WA 98230 tel 360-200-5500	mailing addresses	1080 Cliveden Ave # 6, Delta BC V3M 6G6 tel 604-538-3090
Hainesport NJ, Naples FL, Vancouver WA	warehouses	Delta BC & Mississauga ON