SK | AIR CURTAIN™

CEILING FAN HEATER









HEAT FROM ABOVE

The AIR CURTAIN ceiling fan heater silently beams down heat from above. This unique model is ideal for rooms where wall space is limited. In bathrooms, the AIR CURTAIN can be installed just outside the shower or bathtub. With its ceiling-recessed casing, the AIR CURTAIN is an excellent way to provide discreet air circulation. The result: uniform heating and air movement, and reduction in mirror and window fog. By adding a wall timer, you can use it on demand.

CEILING MOUNTED

IDEAL FOR ROOMS WITH LIMITED WALL SPACE

HEATING ON DEMAND

OPTIONAL WALL TIMER

COMPACT AND QUIET

347 V MODEL AVAILABLE

COLOURS

- standard: white, soft white
- ORORA (optional): refer to www.stelpro.com/en-CA/orora)

FINISH

• epoxy-polyester powdercoat

MANUFACTURING

- 22-gauge steel cabinet and 1/4 in. (6.4 mm) deep 20-gauge steel front grille
- easy access for maintenance (no screws)

THERMAL PROTECTION

• thermal protection with automatic reset

ELEMENT

 nichrome element produces instant heat

CONTROL

- built-in thermostat (optional)
- wall thermostat (not included) the use of an electronic thermostat is strongly recommended
- 60 minute timer (optional)

INSTALLATION

- ceiling mounted (recommended height 8 ft., maximum 9 ft.)
- surface mounted with surface adapter (optional)
- recessed or surface mounted with adapter for suspended ceiling (optional)
- unit can be mounted parallel or perpendicular to ceiling beams
- approved to be recessed in mineral wool; for all other materials please check with insulating product manufacturer

WARRANTY

five years

IDEAL FOR:


bathroom, entryway, daycare centre, room with limited wall space




TECHNICAL SPECIFICATIONS														
WITHOUT CONTROL		BUILT-IN THERMOSTAT		24 V CONTROL		POWER	VOLTAGE	FLOW		ROW	HEAT	EAT RISE WEIGHT		
CODE	PRICE	CODE	PRICE	CODE	PRICE	WATTS	VOLTS	CFM	М	FT.	°C	°F	KG	LB
SK0501	236.00					500	120	60	2.4	8	26	46	5	11
SK0508	236.00					500	208	60	2.4	8	26	46	5	11
SK0502	236.00					500/375	240/208	60	2.4	8	26	46	5	11
SK0503	287.00	SK0503T	360.00	SK0503C24	360.00	500	347	60	2.4	8	26	46	5	11
SK0751	236.00					750	120	60	2.4	8	42	75	5	11
SK0758	236.00					750	208	60	2.4	8	42	75	5	11
SK0752	236.00					750/560	240/208	60	2.4	8	42	75	5	11
SK0753	287.00	SK0753T	360.00	SK0753C24	360.00	750	347	60	2.4	8	42	75	5	11
SK1001	249.00					1000	120	60	2.4	8	54	97	5	11
SK1008	249.00					1000	208	60	2.4	8	54	97	5	11
SK1002	249.00					1000/750	240/208	60	2.4	8	54	97	5	11
SK1003	300.00	SK1003T	373.00	SK1003C24	373.00	1000	347	60	2.4	8	54	97	5	11
SK1251	263.00					1250	120	60	2.4	8	79	143	5	11
SK1258	263.00					1250	208	60	2.4	8	79	143	5	11
SK1252	263.00					1250/940	240/208	60	2.4	8	79	143	5	11
SK1253	314.00	SK1253T	387.00	SK1253C24	387.00	1250	347	60	2.4	8	79	143	5	11
SK1501	270.00					1500	120	60	2.4	8	102	184	5	11
SK1508	270.00					1500	208	60	2.4	8	102	184	5	11
SK1502	270.00					1500/1125	240/208	60	2.4	8	102	184	5	11
SK1503	321.00	SK1503T	394.00	SK1503C24	394.00	1500	347	60	2.4	8	102	184	5	11
						2000	120	90	3.2	10'6"	109	196	5	11
						2000	208	90	3.2	10'6"	109	196	5	11
SK2002	308.00					2000/1500	240/208	90	3.2	10'6"	109	196	5	11
SK2003	359.00	SK2003T	432.00	SK2003C24	432.00	2000	347	90	3.2	10'6"	109	196	5	11

Add W for white or SW for soft white (consult the optional colours chart or contact your °STELPRO representative for all other colours). Models also available in 277 V. --- not available

TECHNICAL DRAWINGS





- * Add W for white or SW for soft white. * Factory installed

