PASS & SEYMOUR®
800 Series Cable Reel



800 Series Cable Reel with Tri-Tap, 40FT, 12AWG, 15A

CR08123N40T15

Delivers simple, reliable power distribution with 40 feet of reach and clear illuminated NEMA 5-15 tri-tap connector, making it easy to support multiple connections and confirm power at a glance. Built with a durable, lightweight nonmetallic enclosure and a detachable swivel mounting bracket, it installs quickly and performs in everyday applications. Designed as a streamlined, single-SKU solution, the 800 Series Cable Reel reduces complexity while meeting core performance needs in data centers, education and light commercial spaces.

Standard Features

- cETL Listed to CSA C22.2 No. 42
- Rugged nonmetallic enclosure
- Detachable swivel mounting bracket
- Rated at 125V, 15A, 1750W
- 15A push button breaker in reel housing
- 12/3 SJTW yellow cord, 105c rated
- Furnished with adjustable ball stop
- Clear illuminated NEMA 5-15 triple tap
- 2 ft. incoming cord with NEMA 5-15 plug
- RoHS Compliant

Applications:


- For dry indoor locations only
- Educational
- Data Center
- Maintenance Shops
- Repair Facilities
- Municipality
- Commercial
- Warehouses
- Retail Facilities




Product Details:



Rugged nonmetallic enclosure



Detachable swivel mounting bracket




15-Amp push button circuit breaker



Clear, Illuminated NEMA 5-15 Tri-Tap

Technical Information

Cable Gauge	Mobile End	GFCI	Length	Cable	Amperage
CR08123N40T15	Tri-Tap	No	40 ft	12AWG	15A



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1-877-295-3472
www.legrand.us

Canada
1-844-977-3783
www.legrand.ca

FOLLOW US

©2026 Legrand