DI1408R5

Inner doors | Floor Standing Enclosures

CONNECT AND PROTECT



H	1400
W	800
Item no.	DI1408R5

Description: Inner door provides a hinged mounting surface for equipment behind a standard or glazed front door. A mounting space of 80 mm, is available between the doors when the inner door is in the most forward position. Can be adjusted in depth by steps of 25 mm. The mounting plate remains usable behind the inner door. The door is equipped with two double-bit 3 mm locks.

Material: 1.5 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 door with mounting accessories.

Displays and indicators can be mounted on a surface within the enclosure while covering other components, and preventing unauthorized access.