CAB Hanger Data Sheet

CAB Part Number	Safe Working Load of Hanger in Pounds*	Safe Working Load of Hanger in Kilograms*	Safe Working Load for Each Individual Carrier in Pounds*	Safe Working Load for Each Individual Carrier in Kilograms*	Typical Single Cable Spacing Interval in Feet	Typical Single Cable Spacing Interval in Meters	Qty/Box	Weight Per Box in Pounds	Weight Per Box in Kilograms
141	67	30			2 to 5	.6 - 1.5	10	23	10
143	67	30			2 to 5	.6 - 1.5	10	20	9
144	67	30			2 to 5	.6 - 1.5	10	21	10
154	160	73	80	36	2 to 5	.6 - 1.5	10	60	27
155	100	45	87	40	2 to 5	.6 - 1.5	25	35	16
156	100	45	87	40	2 to 5	.6 - 1.5	25	41	19
183	80	36			2 to 5	.6 - 1.5	25	28	13
188	100	45	40	18	2 to 5	.6 - 1.5	50	47	21
189	125	57	80	36	2 to 5	.6 - 1.5	10	31	14
199	50	23			2 to 5	.6 - 1.5	100	18	8
205	50	23			2 to 5	.6 - 1.5	50	7	3
213	100	45	87	40	2 to 5	.6 - 1.5	25	31	14
219	52	24			2 to 5	.6 - 1.5	200	19	9
221	100	45			2 to 5	.6 - 1.5	100	17	8
222	100	45			2 to 5	.6 - 1.5	50	14	6
223	59	27			2 to 5	.6 - 1.5	200	17	8
228	100	45	40	18	2 to 5	.6 - 1.5	50	47	21
231	80	36	40	18	2 to 4	.6 - 1.3	25	11	5
243	125	57	80	36	2 to 5	.6 - 1.5	10	25	11
244	125	57	80	36	2 to 5	.6 - 1.5	10	22	10
245	125	57	80	36	2 to 5	.6 - 1.5	10	27	12
250	125	57	80	36	2 to 5	.6 - 1.5	10	30	14
296	60	27			2 to 5	.6 - 1.5	200	15	7
297	60	27			2 to 5	.6 - 1.5	200	15	7
298	110	50			2 to 5	.6 - 1.5	50	9	4
299	110	50			2 to 5	.6 - 1.5	100	15	7
300	110	50			2 to 5	.6 - 1.5	100	13	6
301	110	50			2 to 5	.6 - 1.5	50	18	8
302	60	27			2 to 5	.6 - 1.5	200	16	7
305	80	36	40	18	2 to 4	.6 - 1.3	25	11	5
306	90	41			2 to 5	.6 - 1.3	50	12	6
308	90	41			2 to 5	.6 - 1.5	50	9	4
311	40	18			2 to 5	.6 - 1.5	200	11	5
314	180	82			2 to 5	.6 - 1.5	100	13	6
315	180	82			2 to 5	.6 - 1.5	50	11	5

CAB Part Number	Safe Working Load of Hanger in Pounds*	Safe Working Load of Hanger in Kilograms*	Safe Working Load for Each Individual Carrier in Pounds*	Safe Working Load for Each Individual Carrier in Kilograms*	Typical Single Cable Spacing Interval in Feet	Typical Single Cable Spacing Interval in Meters	Qty/Box	Weight Per Box in Pounds	Weight Per Box in Kilograms
316	100	45			2 to 5	.6 - 1.5	100	17	8
320	90	41			2 to 5	.6 - 1.5	100	15	7
321	90	41			2 to 5	.6 - 1.5	50	9	4
333	45	20			2 to 5	.6 - 1.5	200	12	5
334	40	18			2 to 5	.6 - 1.5	200	12	5
335	100	45			2 to 5	.6 - 1.5	50	11	5
336	100	45			2 to 5	.6 - 1.5	50	13	6
339	56	25			2 to 5	.6 - 1.5	200	16	7
340	40	18			2 to 5	.6 - 1.5	200	11	5
341	40	18			2 to 5	.6 - 1.5	200	11	5
342	60	27			2 to 5	.6 - 1.5	200	10	5
343	100	45			2 to 5	.6 - 1.5	100	47	21
344	100	45			2 to 5	.6 - 1.5	50	12	6
347	87	40			2 to 5	.6 - 1.5	50	29	13
349	60	27			2 to 5	.6 - 1.5	25	18	8
350	40	18			2 to 5	.6 - 1.5	25	23	10
353	87	40			2 to 5	.6 - 1.5	25	17	8
462	60	27			2 to 5	.6 - 1.5	25	21	10
479	40	18			2 to 5	.6 - 1.5	25	30	14
809	80	36	40	18	2 to 4	.6 - 1.3	100	15	7
811	80	36	40	18	2 to 4	.6 - 1.3	25	10	5
812	80	36	40	18	2 to 4	.6 - 1.3	25	10	5
813	80	36	40	18	2 to 4	.6 - 1.3	40	19	9
814	50	23			2 to 5	.6 - 1.5	200	13	6
815	200	91			2 to 5	.6 - 1.5	100	13	6
816	175	80			2 to 5	.6 - 1.5	50	9	4
817	275	125			2 to 5	.6 - 1.5	50	16	7
818	275	125			2 to 5	.6 - 1.5	25	9	4
819	275	125			2 to 5	.6 - 1.5	25	10	5
820	240	109			2 to 5	.6 - 1.5	25	13	6
821	50	23			2 to 5	.6 - 1.5	200	13	6
822	200	91			2 to 5	.6 - 1.5	100	13	6
823	175	80			2 to 5	.6 - 1.5	50	9	4
824	275	125			2 to 5	.6 - 1.5	50	16	7
825	275	125			2 to 5	.6 - 1.5	25	9	4
826	275	125			2 to 5	.6 - 1.5	25	10	5
828	240	109			2 to 5	.6 - 1.5	25	13	6

CAB Part Number	Safe Working Load of Hanger in Pounds*	Safe Working Load of Hanger in Kilograms*	Safe Working Load for Each Individual Carrier in Pounds*	Safe Working Load for Each Individual Carrier in Kilograms*	Typical Single Cable Spacing Interval in Feet	Typical Single Cable Spacing Interval in Meters	Qty/Box	Weight Per Box in Pounds	Weight Per Box in Kilograms
830	340	155			2 to 5	.6 - 1.5	25	15	7
831	500	227			2 to 5	.6 - 1.5	25	37	17
832	500	227			2 to 5	.6 - 1.5	25	39	18
834	140	64			2 to 5	.6 - 1.5	50	10	5
835	140	64			2 to 5	.6 - 1.5	50	11	5
836	140	64			2 to 5	.6 - 1.5	50	12	5
837	140	64			2 to 5	.6 - 1.5	50	13	6
838	140	64			2 to 5	.6 - 1.5	50	14	6
844	155	70			2 to 5	.6 - 1.5	50	13	6
845	155	70			2 to 5	.6 - 1.5	50	14	6
846	155	70			2 to 5	.6 - 1.5	50	16	7
847	155	70			2 to 5	.6 - 1.5	50	18	8
848	155	70			2 to 5	.6 - 1.5	50	20	9
873	N/A	N/A			2 to 5	.6 - 1.5	100	15	7
874	N/A	N/A			2 to 5	.6 - 1.5	50	12	6
893	200	91			2 to 5	.6 - 1.5	100	15	7
894	200	91			2 to 5	.6 - 1.5	100	17	8
895	200	91			2 to 5	.6 - 1.5	50	9	4
896	200	91			2 to 5	.6 - 1.5	50	10	5
897	150	68			2 to 5	.6 - 1.5	100	15	7
898	150	68			2 to 5	.6 - 1.5	100	16	7
900	150	68			2 to 5	.6 - 1.5	50	9	4
902	150	68			2 to 5	.6 - 1.5	50	10	5
903	20	9			2 to 4	.6 - 1.3	200	8	4
904	20	9			2 to 4	.6 - 1.3	200	8	4
905	20	9			2 to 4	.6 - 1.3	50	7	3
906	20	9			2 to 4	.6 - 1.3	50	9	4
908	40	18			2 to 5	.6 - 1.5	200	15	7
909	20	9			2 to 4	.6 - 1.3	50	12	5
910	80	36	40	18	2 to 4	.6 - 1.3	50	9	4
911	40	18			2 to 5	.6 - 1.5	100	11	5
912	40	18			2 to 5	.6 - 1.5	100	10	5
928	52	24			2 to 5	.6 - 1.5	50	32	15
929	210	95			2 to 5	.6 - 1.5	100	16	7
931	100	45			2 to 5	.6 - 1.5	50	10	5
932	100	45			2 to 5	.6 - 1.5	100	15	7
933	120	55			2 to 5	.6 - 1.5	25	9	4