Mounting Options

Eurofase Heating offers a range of heater types and mounting options to suit various applications and installation needs.

Wall & Ceiling Mounting





Our heaters come with 6-inch brackets for easy wall or ceiling mounting. You can install them flat or angle them at 30° or 45° to deliver warmth exactly where you want it.

Compatible Models: *Eurofase EF & LP Series.*



Recessed Mounting



Recessed installations provide a sleek, minimalist aesthetic, ideal for contemporary residential, commercial, or hospitality settings. Eurofase offers a certified turnkey solution with flush mount kits, fire-rated boxes, and all necessary mounting accessories for an easy, professional installation.

Compatible Models: *Eurofase EF Series.*

Note: *Décor plates are not compatible with recessed mounting.*




Suspension Mounting

For sloped or vaulted ceilings, or spaces with ceilings higher than 12 feet, Eurofase's telescopic suspension kits offer a perfect solution. These kits allow for level mounting on uneven surfaces, ensuring safe, even heat distribution in a complex ceiling environment.

Compatible Models: *Eurofase EF & LP Series.*





Pole Mounting

If wall or ceiling installation isn't an option, pole mounting provides a durable and flexible solution. Eurofase poles are 8 feet tall, available in single or dual-head configurations, and feature concealed wiring. Outdoor switches can be mounted directly on the pole, and heaters may be angled at 0°, 15°, 30°, 45°, or 60° for optimal performance.

Compatible Models: *Eurofase EF & LP Series.*





Control System

Choose from our range of control options to match your desired level of convenience, functionality, and budget. Whether you prefer simple on/off control or advanced smart features, we have a solution that fits your needs.

Basic Controls

Single Paddle Switches: Heavy-duty switches rated for 20 amps, provide simple on/off functionality for single-element heaters.

Duplex/Stacked Switches: Heavy-duty switches rated for 30 amps, allow independent control of each element in dual-element heaters, offering on/off and high/low settings.



Indoor & Outdoor Rated | UL LISTED | CSA

Smart Controls

Smart Wi-Fi/Bluetooth Controller: Requires one module per heater. This cost-effective upgrade provides smart functionality, including on/off, high/low settings, programmable dimming timer, and a 4-hour auto shut-off. Multiple heaters can be seamlessly managed through the Eurofase Heating app.



Android | iOS | Indoor & Outdoor Rated | Intertek | works with Google Home | WORKS WITH alexa | Dimmable

Advanced Controls

Contactor Box:

Functions as a sub-panel, enabling zoning of heaters. Compatible with on/off switches, wall timers, programmable sequential timers, and more. Supports smart home integration, with each zone handling up to 40 Amps.



LUTRON | CRESTRON | Control4

+ Other Smart Home Systems

Indoor & Outdoor Rated | Intertek

Universal Relay Panel:

Functions as a sub-panel with zoning capability. Designed for smart home integration and compatible with dimmers, timers, and other control options to adjust heat intensity. Each zone supports up to 50 amps.



LUTRON | CRESTRON | Control4

+ Other Smart Home Systems

Indoor & Outdoor Rated | Intertek | 0-10V Dimmable | TRIAC Dimmable

* All third-party trademarks, including Lutron®, Crestron®, Control4®, Android™, Apple®, iOS®, Bluetooth®, ETL®, Google Home™, and Alexa®, are the property of their respective owners and are used for compatibility reference only. Use of these marks does not imply endorsement.