6. ORDERING INFORMATION

SE-704-0□-□□

- Conformal Coating:
  Blank – Partial Conformal Coating
  CC – Full Conformal Coating
- Supply:
  3 – 24-Vac Supply
  U – Universal 120/240-Vac/Vdc Supply
  D – 12/24-Vdc Supply
  T – 48-Vdc Supply

ELCT30-31	Current Sensor, 31 mm (1.22 in.) window
ELCT30-88	Current Sensor 88 mm (3.46 in.) window
PGA-0500	Analog Percent Current Meter (PGA-05CV included)
PMA-55	Panel-Mount Adapter, NEMA 1
PMA-60	Panel-Mount Adapter, NEMA 3, IP53. Includes two TR20 tamper-resistant Torx screws and two thumb screws.
AC700-HW-00	TR20 tamper-resistant Torx, 0.25 in. insert bit
AC700-HW-01	TR20 tamper-resistant Torx driver
PMA-3	Adapter Plate, GEC/MCGG
PMA-6	Adapter Plate, FPL-GFRM
PMA-15	Adapter Plate, MGFR

Consult factory for custom mounting adapters.

7. WARRANTY

The SE-704 Earth-Leakage Monitor is warranted to be free from defects in material and workmanship for a period of five years from the date of purchase.

Littelfuse will (at Littelfuse's option) repair, replace, or refund the original purchase price of an SE-704 that is determined by Littelfuse to be defective if it is returned to the factory, freight prepaid, within the warranty period. This warranty does not apply to repairs required as a result of misuse, negligence, an accident, improper installation, tampering, or insufficient care. Littelfuse does not warrant products repaired or modified by non-Littelfuse personnel.