
## **PL17 Series**


## 100 A 600 V; Polyphase

## **Product Specifications**

- Conductor range: 6-1/0 AWG
- · Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground
- Supplied with screw type ring
- Weatherproof Type 3R enclosure
- · Primarily used in: All provinces




1-3/16 in.





(PL17-INV)



COMBINATION AND UNDERGROUND BOTTOM



Cat. No.	Description	D	Dimensions (in.)			Weight Each	
		Н	W	D	lb.	kg	
7 JAW							
PL17-INV	Overhead, hub opening		8-9/16	5-7/16	12	5.4	
PL17-INV-HQ	Overhead, hub opening (Hydro-Québec approved)						
PL17-INTV-HQ	Underground (Hydro-Québec spec)						
PL17-INTCV	Combination overhead-underground	15-5/8					
PL17-INTCV-HQ	Combination overhead-underground (Hydro-Québec approved)	10-0/6					
PL17-V	Overhead, hub opening						
PL17-TV	Underground						
PL17-TCV	Combination overhead-underground						
<b>FACTORY INSTALLE</b>	ACCESSORIES						
Include: -IN	Insulated neutral						