Conduit Knockouts









BCOBEX

Octagonal box extension.

BC56111

Ceiling pan.

Concentric knockouts.

CI54151-KSSX

Concentric knockouts. "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.











BC55151-K

Extension ring with ground screw. Concentric knockouts.

BC54171-K

Concentric knockouts.

Concentric knockouts. "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support

CI54171-KSSX

CI54171-KSSX-1

Mounting strap (offset for 2 x 1/2 in. drywall thicknesses).

CI55171-K

Extension ring with ground screw. Concentric knockouts.



| Cat. No. | Description |
|---------------------------|-------------------------------------------------------------------------------------------------------|
| 1/2 in. Deep — Extensions | |
| BCOBEX | Extension for octagonal boxes. 1/2 in. non-adjustable depth Complete with mounting screws (5 cu. in.) |

| Cat No | Volume | Features | | Knockouts | | | | | |
|----------------|-----------|----------|---------------------|---------------|----------------|---------------|----------------|--|--|
| | (Cu. in.) | Bracket | Raised Ground Screw | 1/2 in. sides | 1/2 in. bottom | 3/4 in. sides | 3/4 in. bottom | | |
| 1-1/2 in. Deep | | | | | | | | | |
| BC56111 | 5.0 | - | yes | - | 4 | - | - | | |
| 1-1/2 in. Deep | | | | | | | | | |
| BC54151-K | 15.0 | - | yes | 4 | 4 | 2 | 2 | | |
| CI54151-KSSX | 15.0 | "SSX" | yes | 2 | 4 | 2 | 2 | | |
| BC55151-K | 15.0 | - | yes | 4 | - | 2 | - | | |
| 2-1/8 in. Deep | | | | | | | | | |
| BC54171-K | 21.0 | - | yes | 4 | 4 | 2 | 2 | | |
| CI54171-KSSX | 21.0 | "SSX" | yes | 2 | 4 | 2 | 2 | | |
| CI54171-KSSX-1 | 21.0 | "SSX-1" | yes | 2 | 4 | 2 | 2 | | |
| CI55171-K | 21.0 | - | ves | 4 | - | 2 | - | | |





Nonmetallic Sheathed Cable Clamps





Prepositioned depth tabs recessed 1/2 in.



BC54151-LB

Side bracket, with holding prongs and prepositioned depth tabs.



BC54151-LD

Swing-arm" rework brackets. Max. wall thickness: 3/4 in.. Max. load capacity: 12 lb. (5.5 kg).



BC54171-L



BC54171-LB

Side bracket, with holding prongs.



CI54171-LF

Ceiling fan box. (Supplied with 2 #10-32 machine screws and star washers.) Max. load capacity: 35 lb. (15.6 kg).



| | Volume | Features | | Knockouts | | Pryouts | |
|----------------|-----------|----------|---------------------|---------------|----------------|---------|--------|
| | (Cu. in.) | Bracket | Raised Ground Screw | 1/2 in. sides | 1/2 in. bottom | sides | bottom |
| 1-1/2 in. Deep | | | | | | | |
| BC54151-L | 15.0 | - | yes | 2 | 1 | 4 | 4 |
| BC54151-LB | 15.0 | "B" | yes | 1 | 1 | 4 | 4 |
| BC54151-LD | 15.0 | rework | yes | - | 1 | 4 | 4 |
| CI54151-LF | 15.0 | - | yes | 2 | 1 | 4 | 4 |
| 2-1/8 in. Deep | | | | | | | |
| BC54171-L | 21.0 | - | yes | 2 | 1 | 4 | 4 |
| BC54171-LB | 21.0 | "B" | yes | 1 | 1 | 4 | 4 |
| BC54171-LD | 21.0 | rework | - | - | 1 | 4 | 4 |
| CI54171-LF | 21.0 | - | yes | 2 | 1 | 4 | 4 |

FOR USE WITH NONMETALLIC SHEATHED CABLE ONLY

Note: CEC 2012 rule 30-302: Subrule (4) requires that a ceiling-mounted luminaire weighing 23 kg or less be supported on a ceiling outlet box attached directly to the building structure. A bar hanger may also be used to attach a ceiling outlet box to the building structure when the luminaire weighs 23 kg or less.



Armoured and Nonmetallic Sheathed Cable Clamps







BC54151-LSSAX

"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs.
With integral support bracket.



BC54171-LA



BC54171-LSSAX



BC54171-LSSAX-5/8

Brackets for use with 5/8 in. drywall.



| Cat. No. | Volume | Features | | Knockouts | | Pryouts | |
|-------------------|-----------|----------|---------------------|---------------|----------------|---------|--------|
| | (Cu. in.) | Bracket | Raised Ground Screw | 1/2 in. sides | 1/2 in. bottom | sides | bottom |
| 1-1/2 in. Deep | | | | | | | |
| BC54151-LA | 15.0 | - | yes | 2 | 1 | 4 | - |
| BC54151-LSSAX | 15.0 | "SSX" | yes | - | 1 | 4 | - |
| 2-1/8 in. Deep | | | | | | | |
| BC54171-LA | 21.0 | - | yes | 2 | 1 | 4 | - |
| BC54171-LSSAX | 21.0 | "SSX" | yes | - | 1 | 4 | - |
| BC54171-LSSAX-5/8 | 21.0 | "SSX" | yes | - | 1 | 4 | - |



Covers





| Cat. No. | Description | | | | |
|-----------------------------------------|----------------------------------------------------------------------------------------|--|--|--|--|
| 4 in. Round Covers | | | | | |
| BC54-C-1 | Flat blank | | | | |
| BC54-C-6 | Flat with 1/2 in. conduit knockout | | | | |
| CI54-C-64 | Flat for 1-13/32 in. diameter. 15 A single receptacle. Device mounting screws included | | | | |
| BC54-C-65 | Flat for duplex receptacle. Device mounting screw included | | | | |
| BC54-C-94 | Flat for toggle switch. Device mounting screws included | | | | |
| 5 in. Round Covers (White Enamel Paint) | | | | | |
| BC54-COV | Flat with 1/2 in. conduit knockout. Mounting screws included | | | | |
| BC54-COV-1 | Flat blank. Mounting screws included | | | | |