



## **Stainless Steel Sealing Rings**

Cat. No.	Description
MSR-C2	Stainless steel sealing ring, tamper-proof

## **Polycarbonate Sealing Ring**

Cat. No.	Description
S102WD	Ring, available with any meter socket

When ordering any meter socket, add suffix "Z" to meter socket cat. no. to exchange standard stainless steel ring for S102WD model.



# **Meter Protectors**

## **Product Specifications**

- Meter protector for use in problem areas (trailer parks, playgrounds, conservation areas)
- Steel construction (16 ga. galv. steel)
- Clear, unbreakable polycarbonate front cover, which allows full view of meter revenue reading and serial number
- Sealing and padlocking provision
- Grey painted

Cat. No.	Description
MP01	7-1/6 in. dia. x 4-3/4 in. deep for use with single phase residential meters
MP02	7-1/6 in. dia. x 8-3/4 in. deep for use with all meters, other than single phase residential meters



#### BS087 / BS089 / BS090



**CM-BS100** 





**MH10X** 



## **Blank Meter Cover Plates**

Cat. No.	Description
BS087	Grey ABS
BS089	Plastic "throw-away" cover
BS090	Clear unbreakable polycarbonate

Not recommended as a permanent cover for energized meter sockets.

## **Jumper Bar**



Cat. No.	Description
CM-BS100	200 A Max.

## **Mast Coupler**



Cat. No.	Description
MH200	Fits all sockets with regular 2-1/2 in. hub opening

#### **Mast Hubs**



Cat. No.	PVC Cat. No.	A Hub Size (in.)	В
MH10X	_	1	
MH12X	E991G	1-1/4	For 2-1/2 in. regular hub opening
MH15	E991H	1-1/2	(add hub adapter plate BS052 if used
MH20	E991J	2	with units having 4 in. hub openings)
MH25	E991K	2-1/2	
MH30	E991L	3	
MH35	_	3-1/2	For 4 in. hub opening
MH40	_	4	

Supplied with 4 Robertson head screws.

# **Hub Adapter Plate**



Cat. No.	Description
BS052	Permits use of regular size hubs on larger hub openings













Consist of thermoplastic insulators with jaws and connectors assembled for replacement of one meter socket

# **Accessories**

## **Hub Opening Closure Plates**



Cat. No.	Description	
BS051	Inside attachment for regular hub opening (i.e.: 1 in. to 2-1/2 in.)	
BS054	Inside attachment for larger hub opening (i.e.: 3 in. to 4 in.)	

#### **Insulated Neutral Kits**



Cat. No.	Description
IN1000BA, IN1000BE, IN1000PL	100 A Max.
IN2000BS, IN2000PL	200 A Max.
IN4000BS	400 A Max.

Specify socket upon ordering.

## **Insulated Neutral Kit**



Cat. No.	Description
IN4000JS	400 A Max. (JS4)

## **Ground Lug On Neutral Kit**

Cat. No.	Description
GN2000	200 A Max. for BQ2, BS2 Series

#### **Identification Marker Kits**


Cat. No.	Description	Markers Kit Includes	Qty.	
MINI-ID-KIT	Plastic case	Stainless steel markers of each numbers 0 thru 9 (dash + service)	10	
MICRO-ID-KIT	Blue metal	Stainless steel markers of each letters A thru D		
		Stainless steel markers of each numbers 0 thru 9	10	
		Words "SERVICE"		
	carrying case	CM-BS100 Jumper Bar 200 A Max.	4	
		LS500 Meter Jaw Safety Shroud	10	

Supplied with 4 Robertson head screws.

#### **Identification Markers**

Cat. No.	Description		
No. 0 through No. 9	Clipped to the upper lip of the enclosure; provides permanent customer identification. Packed and sold in polyethylene bags of 10 identical markers except "SERVICE" which		
No. A through No. Z			
No. SERVICE	has 7 individual letters		





## Ready-to-install replacement block assemblies



Cat. No.	Description
BA3-X	Fits BA3 / BE1 Series

Add suffix "B" to cat. no. above if mounting bridge is required



Cat. No.	Description
BS2-X-UNI	Fits BQ2 / BS2 Series uni block
Add suffix "R" to cat no above if mounting bridge is required	



Cat. No.	Description
<b>BS2-XBGN-UNI</b>	Neutral 200 A

Add suffix "B" to cat. no. above if mounting bridge is required



Cat. No.	Description
Gat. NO.	Description
MO2-X-UNI	Fits MO2 Series uni block

Add suffix "B" to cat. no. above if mounting bridge is required



Cat. No.	Description	
PL17X	Neutral 200 A	

Add suffix "B" to cat. no. above if mounting bridge is required



Cat. No.	Description
PL27-XEB	Fits PL27 Series uni block

Add suffix "B" to cat. no. above if mounting bridge is required



## **Repair Kits**

## **Replacement Part Kits**

Cat. No.	For Meter Socket	Component*
REPAIR KIT BE1-TCV	BE1-TCV	BS2027, CDA110, BONDLUG2, SCREW-BS1002
REPAIR KIT BQ2-V	BQ2-V	BS2027, BS2611L, BONDLUG2, SCREW-BS2402
REPAIR KIT BQ2-VGN	BQ2-VGN	BS2027, BS2411GN, BONDLUG2, SCREW-BS2402
REPAIR KIT BS2-TCV	BS2-TCV	BS2027, BS2611L, BONDLUG2, SCREW-BS2402
REPAIR KIT BS2-TCVBC	BS2-TCVBC	BS2027, BS2611L, NA75Z-3, SCREW-BS2402
REPAIR KIT MO2V/VO	M02V/V0	BS2027, BS8608, BONDLUG2, SCREW-BS2402

## You can also order the components separately

## **Bond Lug**

Cat. No.	Description
<b>BONDLUG2-FG</b>	Bond lug to be used in BE1,BQ2,BS2,MO2
NA75Z-3-FG	Bond lug to be used in BS2-TCVBC

## **Neutral Lug**

Cat. No.	Description
BS8608-FG	Neutral for MO2 200 A
CDA110-FG	Neutral for BE1 100 A

#### **Shroud**

Cat. No.	Description
BS2027-FG	Red meter jaw safety shroud

#### **Set Screw**

Cat. No.	Description
SCREW-BS1002-FG 100A	Set screw only for 100 A lugs
SCREW-BS2402-FG 200A	Set screw only for 200 A lugs

## **Neutral**

Cat. No.	Description
BS2611L-FG	Neutral 200 A
BS2411GN-FG	Neutral 200 A C/W Ground





BS8608-FG





BS2027-FG





**SCREW-BS2402-FG 200A** 











<sup>\*</sup> Each part comes in a bag of 10
Easy to reorder. Simply add suffix **-FG** to the components listed in the kit.

#### **Fifth Jaw Assemblies**



Meter Socket Series	Standardcapacity 9 o' position	Full capacity 9 o' position Z105* Z205*		Full capacity 6 o' position	
361163	C205			CM-B106*	B306*†
BA3	•	•			
BDC	•		•		•
BE1	•	•		•	
BE2	•	•			
BEC	•	•			
BD2	•		•		•
BQ2	•		•		•
BS2 / BS2L	•		•		•
BS4 / BSC4	•		•		•
C01	•	•		•	
C02	•		•		•
CO1 Multigang	•	•		•	

<sup>\*</sup> CSA not applicable † For mono blocks only

#### **Pole Mount Bracket Kit**

Cat. No	Description	Conductor Range	Use w/Series	Option 1	Option 2
PMB200	Secures Microlectric meter socket to a wooden pole via Option 1 or 2	14-2 AWG	BA3, BE1, BQ2, BS, CL, C01, C02, CT, M02, PL17, PL27, VT	Use a lag bolt through 5/8 in. center keyhole	Use the two side bracket mounting holes (0.320 in. dia.) to wrap around the pole

Suitable for any Microlectric meter socket with mounting holes 5 in. apart. Attach meter socket using one or two bracket(s). PMB200 kit comes complete with 2 brackets, 1 ground connector. Includes assembly hardware.

## **Pole Mounting Kit**

Cat. No.	Kit Includes	Weight		Other
	Kit iliciudes	lb.	kg	Qty.
	Support hangers			2
PMBJS4	1/2 in. x 4 in. lag bolt		1	
PIVIBJ54	3/8 in. x 3 in. lag bolt			4
	5/16 in. x 1 in. carriage bolts, nuts and lock washers			
PMB6X12	6 in. offset from pole c/w 12 in. strut	7.7	3.5	
PMB6X24	MB6X24 6 in. offset from pole c/w 24 in. strut 9.2		4.2	1
PMB9X12	MB9X12 9 in. offset from pole c/w 12 in. strut 9.2		4.2	'
PMB9X24	9 in. offset from pole c/w 24 in. strut	11.0	5.0	



**Fifth Jaw Assemblies** 



**PMB200** 



PMBJS4




PMB6X12


#### **Pole Line Hardware**

Cat. No.	Description	F Dia. (in.) G Dia.	G Dia. (in.)	) H Dia. (in.)	T Thick (in.)	Weight (100 pcs)		Std. Pkg.
Gal. NO.	Description	r via. (III.)	u Dia. (III.)	n Dia. (III.)	I THICK (III.)	lb.	kg	Stu. Pky
RC729	Square washer	5/8	2	_	3/16	22	10.0	400
BC301L	Carriage bolt	3/8	1-1/2	1-1/2		11	5.0	
B0506	Oval eye bolt 5/8		6	3	_	122	55.4	50
B0508		F/0	8	4		136	61.8	
B0510		3/6	10	4		150	68.1	
B0512			12	4		168	76.3	1
, C	<b>→</b>		) 9 mmmm	F		<b>&gt;</b>		 

**G**→







RC729 BC301L BO Series

#### CO3417M-1-FG



CO2FB-KIT





CO3009-KIT



CO3409FB-KIT

CO3009A2-KIT



**BP250** 





CIEFA-1/2 / CIEFA-4 CIEFSA-1/2 / CIEFSA-4

<b>KO Conf</b>	KO Configuration				
000		000			
1/2 in.	3/4 in 1-1/4 in.	1-1/2 in., 2 in.	2 -1/2 in., 4 in.		

# **Accessories**

# **Breaker Mounting Bracket**

Cat. No.	Description
C03417M-1-FG	Adjustable Mounting Bracket for CO2 Series to adapt to Siemens, SD and Cutler Hammer breakers

## **Flexible Braid and Conductor Kits**

Cat. No.	Description
CO2FB-KIT	Connection wires adaptor kit for CO2 Series meter sockets for field installation. To be used with Cutler Hammer breakers
C03009-KIT	Siemens breaker conductor kit (breakers not included)
CO3009SD-KIT	Square D breaker conductor kit (breakers not included)
CO3409FB-KIT	Eaton breaker flexible braid kit (breakers not included)
C03009A2-KIT	ABB breaker conductor kit (breakers not included)

#### **Connector Kit**

Cat. No.	Description
BP250	Connector kit 2 x 250 kcmil

## **Service Entrance Heads**

Cat. No.	No. Trade Size			
Service Entrance Heads (Cast Aluminum) Rigid Conduit				
CIEFA-1/2 1/2				
CIEFA-3/4	3/4			
CIEFA-1	1			
CIEFA-1 1/4	1-1/4			
CIEFA-1 1/2	1-1/2			
CIEFA-2	2			
CIEFA-2 1/2	2-1/2			
CIEFA-3	3			
CIEFA-3 1/2	3-1/2			
CIEFA-4	4			

Trade Size	KO Dimensions				
	Small	Large	Center		
1/2	0.312	_			
3/4	0.375	0.400			
1	0.400	0.500	_		
1-1/4	0.438	0.625			
1-1/2	0.610	0.750	0.400		

Cat. No.	Trade Size	
Service Entrance Heads (Cast Aluminum) E.M.T.		
CIEFSA-1/2	1/2	
CIEFSA-3/4	3/4	
CIEFSA-1	1	
CIEFSA-1 1/4	1-1/4	
CIEFSA-1 1/2	1-1/2	
CIEFSA-2	2	
CIEFSA-2 1/2	2-1/2	
CIEFSA-3	3	
CIEFSA-3 1/2	3-1/2	
CIEFSA-4	4	

Trade Size	KO Dimensions			
	Small	Large	Center	
2	0.750	1.000	0.525	
2-1/2	0.875	1.300	1.000	
3				
3-1/2	1.125	1.750	1.125	
4				