


### **Service Entrance Masts and Accessories**

Reference No.	Cat. No.	lb./kg 100 pcs	Std. Pkg.	Description	
	MM104	105/47.1	20	1-1/4 in. Entrance cap 100 A	
1	MM105	130/59	10	1-1/2 in. Entrance cap 150–200 A	
	MM202	200/90	10	2 in. Entrance cap 200 A	
2	MM380	50/22.7	50	Guy attachement c/w oval eye	
	MM380A		30	Guy attachement without oval eye complete with bracket	
	MM101	125/56	20	Light duty spool rack 100 A	
3	MM5101	164/74		Light duty spool rack (Alberta only) 100 A	
	MM201	300/136	10	Heavy duty spool rack 200 A	
	MM801	360/163	10	Heavy duty spool rack 400 A, fits 4 in. Rigid conduit	
4	MM390	50/22.7	50	Drop wire hook bracket	
5	MM300	100/45.4	20	Service mast wire holder	
6	MM500	14/6.3	50	Neoprene collar only	
	MM501	36/16.3	30	Steel collar only	
7	MM502	150/68		Roof base flange only	
	MM503	180/81	10	Roof flange C/W steel collar	
8	MM505N	140/63		Roof flange C/W neoprene collar	
	MM5505N	140/63		Roof flange C/W neoprene collar 1-1/4 in.	
9	MM250	125/56	20	1/2 in. dia. «U» bolt mast clamp	
	MM251	40/18.1		Pipe strap C/W two 3/8 in. x 4 in. lag screws	
10	MM255	40/18.1	50	Pipe strap C/W two 3/8 in. x 5 in. lag screws	
	MM252	30/13.6		Pipe strap only less lag screws	
	MM400	225/102		Support clamp C/W 5/8 in. x 10 in. fully threaded bolt and 4 in. x 4 in. square washer	
11	MM401	110/50	20	Clamp only less bolt and washer	
• • • • • • • • • • • • • • • • • • • •	MM445	215/97	20	Support clamp C/W 5/8 in. x 4-1/2 in. fully threaded bolt and 4 in. x 4 in. square washer	
	MM5400	213/31		Support clamp C/W 1/2 in. x 10 in. bolt	
	MM8	2800/1272	50	8 ft. x 2-1/2 in. outside diameter mast	
12	MM9CM	3300/1500		9 ft. x 2-1/2 in. outside diameter mast	
12	MM10	3500/1590		10 ft. x 2-1/2 in. outside diameter mast	
	MM12	4200/1909		12 ft. x 2-1/2 in. outside diameter mast	
	MM600	235/106		Meter spacer complete with pipe strap; 5/8 in. x 4-1/2 in. carriage bolt and 4 in. x 4 in. square washer	
	MM601	190/86		Same as above except no pipe strap	
13	MM602	150/68	20	Spacer only (less strap, bolt and washer) (suggested for brick applications with MM201 less pipe strap)	
	MM602LD	119/54		Light duty spacer only (less strap, bolt and washer)	
	MM603	200/90		Spacer with pipe strap (less bolt and washer)	
	MM100	36/16.3		1 in. Female reducer	
	MM140			1-1/4 in. Female reducer	
	MM140M			1-1/4 in. Male reducer	
14	MM150	44/20	25	1-1/2 in. Female reducer	
	MM150M	44/20		1-1/2 in. Male reducer	
	MM200			2 in. Female reducer	
	MM200M			2 in. Male reducer	
45	MH200	40/18	1	2 in. Mast adaptor	
15	MH40	103/46.82	10	4 in. Mast coupler	
16	MM506N	52/23.6		Simple all neoprene roof flange, 200 A, for 2-1/2 in. masts	
16	MM806N	100/45	10	Simple all neoprene roof flange, 400 A, for 4 in. masts	
17	MM507DN	93/42.3	10	Double all neoprene roof flange; for 2-1/2 in. masts	
18	MM604	150/68		Meter socket bracket (Dimensions see page D52)	
19	MM605	50/22.7	25	Meter socket mounting bracket (Dimensions see page D52)	
20	MM700	85/38.6	50	Service mast ground clamp, wire range: 8-1/0 AWG	
24	MM202P	200/90	10	2 in. entrance cap for old style 2-3/4 in. service masts	
21	CIEFA-4	590/268	1	4 in. entrance head	
22	MM200P	44/20	20	2 in. female reducer for old style 2-3/4 in. service masts	
23	MC250	45/21	30	2-1/2 in. one-piece coupler (check the installation standards in your region before using the product)	

**Guy Kits for 2-1/2 in. Masts** 



Cat. No.	Qty.	Consists of	Description
1/4 in. Guy Kit			
	1	MM380	Mast Guy Attachment
	2	GT516	Guy Thimbles
		GE14	Guy End
MM914		GW14110	20 ft. of 1/4 in. Guy Wire
	1	GC902	Guy Clamp
		RB404	Roof Bracket
		T404-CM	Lag Screw
5/16 in. Guy Kit			
	1	MM380	Mast Guy Attachment
		GT516	Guy Thimble
		GE516	Guy End
MM9516		GW516110	20 ft. of 5/16 in. Guy Wire
		GC902	Guy Clamp
		BTE512	5/8 in. x 12 in. Bent Thimble Eye Bolt
		RA725	Round Washer





### **Mast Kits Suitable for British Columbia**

Cat. No.	Qty.	Consists of	Description
		MM104	Entrance Cap
	1	MM101	Light Duty Rack
KIT-100BCMH		MM505N	Flange c/w Neoprene Collar
	3	MM250	"U" Bolt Clamp
		MH200	Mast Coupler
	1	MM104	Entrance Cap
	'	MM101	Light Duty Rack
KIT-100BCMN		MM505N	Flange c/w Neoprene Collar
	3	MM250	"U" Bolt Clamp
		MM140	1-1/4 in. Female Reducer
	1	MM104	Entrance Cap
	'	MM101	Light Duty Rack
MMK1-NMH		MM505N	Flange c/w Neoprene Collar
	3	MM400	Support Clamp
	1	MH200	Mast Coupler
		MM202	Entrance Cap
	'	MM201	Heavy Duty Rack
KIT-200BCMH		MM505N	Flange c/w Neoprene Collar
	3	MM250	"U" Bolt Clamp
		MH200	Mast Coupler
	1	MM202	Entrance Cap
	'	MM201	Heavy Duty Rack
MMK2-NMH		MM505N	Flange c/w Neoprene Collar
	3	MM400	Support Clamp
	1	MH200	Mast Coupler



#### **Mast Kits Suitable for Alberta**

### KIT-1 1/4 - 100 A

Cat. No.	Qty.	Consists of	Description				
This mast kit is used in conjunction with 1-1/4 in. rigid conduit							
		MM5104A	1-1/4 in. Throat Entrance Cap				
KIT-1 1/4	4	MM5101	Light Duty Spool Rack				
KII-I 1/4	1	MM5505N	Roof Flange c/w Neoprene Collar				
		MM5400	Support Clamp c/w 1/2 in. x 10 in. Bolt				

### **KIT2-CM - 100 A**

Cat. No.	Qty.	Consists of	Description			
This mast kit is used in conjunction with 2 in. rigid conduit						
	1	MM5104B	2 in. Throat Entrance Cap			
		MM5101	Light Duty Spool Rack			
KIT2-CM		MM505N	Roof Flange c/w Neoprene Collar			
	2	MM5400	Support Clamp c/w 1/2 in. x 10 in. Bolt			
	1	MM5140	1-1/4 in. Bottom Female Reducer			

### KIT-2-AL - 200 A

Cat. No.	Qty.	Consists of	Description
		MM202	Entrance Cap
	1	MM5101	Light Duty Spool Rack
KIT-2-AL		MM505N	Roof Flange c/w Neoprene Collar
	2	MM5400	Support Clamp c/w 1/2 in. x 10 in. Bolt
	1	MM200M	2 in. Reducer

#### MB-110 - 100 A

Cat. No.	Qty.	<b>Consists of</b>	Description
		MM104	1-1/4 in. Entrance Cap
	1	MM201	Heavy Duty Spool Rack
MB-110		MM505N	Roof Flange c/w Neoprene Collar
INID-110	3	MM400	Support Clamp c/w 5/8 in. x 10 in. Fully Threaded Bolt and 4 x 4 Washer
	1	MM140	1-1/4 in. Female Reducer



KIT-1 1/4



KIT2-CM



KIT-2-AL





### Mast Kits Suitable for Manitoba and Saskatchewan

Cat. No.	Qty.	Consists of	Description
		MM104	Entrance Cap
	1	MM140M	1-1/4 in. Reducer
KIT-100MJ	Į į	MM101	Light Duty Rack
KIT-TOOMS		MM505N	Flange c/w Neoprene Collar
	2	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolt
	1	MM400	Support Clamp
		MM104	Entrance Cap
	1	MM140M	1-1/4 in. Reducer
KIT-100MN	ı	MM101	Light Duty Rack
		MM505N	Flange c/w Neoprene Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolt
		MM104	Entrance Cap
	1	MM101	Light Duty Rack
KIT-100MH		MM505N	Flange c/w Neoprene Collar
	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolt
	1	MH200	Mast Coupler
		MM202	Entrance Cap
	1	MM201	Heavy Duty Rack
KIT-200AM	'	MM200M	2 in. Male Reducer
		MM505N	Flange c/w Neoprene Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolt
		MM202	Entrance Cap
	1	MM201	Heavy Duty Rack
KIT-200MH		MM505N	Flange c/w Neoprene Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolt
	1	MH200	Mast Coupler
		MM202	Entrance Cap
		MM200M	2 in. Male Reducer
KIT-200MJ	1	MM201	Heavy Duty Rack
KIT-200MJ	ı	MM505N	Flange c/w Neoprene Collar
		MM251	Strap c/w 3/8 in. x 4 in. Lag Bolt
		MM400	Support Clamp
		MM202	Entrance Cap
	1	MM201	Heavy Duty Rack
MMK2-NMH		MM505N	Flange c/w Neoprene Collar
	3	MM400	Support Clamp
	1	MH200	Mast Coupler





### **Mast Kits Suitable for Ontario**

Cat. No.	Qty.	Consists of	Description
		MM104	Entrance Cap
		MM140M	1-1/4 in. Male Reducer
KIT-100HDM	1	MM201	Heavy Duty Rack
		MM503	Flange c/w Steel Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolts
		MM104	Entrance Cap
	1	MM101	Light Duty Rack
KIT-100MH		MM505N	Flange c/w Neoprene Collar
	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolt
	1	MM200	Female Reducer
		MM104	Entrance Cap
	1	MM140M	1-1/4 in. Male Reducer
KIT-100MN	'	MM101	Light Duty Rack
		MM505N	Flange c/w Neoprene Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolt
		MM104	Entrance Cap
		MM101	Light Duty Rack
KIT-100NMH	1	MM505N	Flange c/w Neoprene Collar
		MM400	Support Clamp
		MM200	Female Reducer
		MM104	Entrance Cap
	1	MM101	Light Duty Rack
MMK1	'	MM140M	1-1/4 in. Male Reducer
		MM503	Flange c/w Steel Collar
	3	MM400	Support Clamp
		MM104	Entrance Cap
	1	MM101	Light Duty Rack
MMK-1N		MM505N	Flange c/w Neoprene Collar
	3	MM400	Support Clamp
	1	MM140M	1-1/4 in. Male Reducer
		MM104	Entrance Cap
	1	MM101	Light Duty Rack
MMK1-NMH		MM505N	Flange c/w Neoprene Collar
	3	MM400	Support Clamp
	1	MH200	Mast Coupler
		MM202	Entrance Cap
	1	MM201	Heavy Duty Rack
KIT-200MH	'	MM200M	2 in. Male Reducer
		MM505N	Flange c/w Neoprene Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolt
		MM202	Entrance Cap
	1	MM201	Heavy Duty Rack
KIT-200AM		MM505N	Flange c/w Neoprene Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolt
	1	MH200	Mast Coupler

Cat. No.	Qty.	<b>Consists of</b>	Description
	1	MM202	Entrance Cap
		MM201	Heavy Duty Rack
KIT-200NMH		MM505N	Flange c/w Neoprene Collar
	3	MM400	Support Clamp
	1	MM200	Female Reducer
		MM202	Entrance Cap
	4	MM201	Heavy Duty Rack
MMK2	1	MM200M	2 in. Male Reducer
		MM503	Flange c/w Steel Collar
	3	MM400	Support Clamp
	1	MM202	Entrance Cap
		MM201	Heavy Duty Rack
MMK-2N		MM505N	Flange c/w Neoprene Collar
	3	MM400	Support Clamp
	1	MM200M	2 in. Male Reducer
		MM202	Entrance Cap
	1	MM201	Heavy Duty Rack
MMK2-NMH		MM505N	Flange c/w Neoprene Collar
	3	MM400	Support Clamp
	1	MH200	Mast Coupler



### **Mast Kits Suitable for Quebec**

Cat. No.	Qty.	Consists of	Description
		MM104	Entrance Cap
	1	MM140M	1-1/4 in. Male Reducer
KIT-100MN		MM101	Light Duty Rack
		MM505N	Flange c/w Neoprene Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolts
		MM104	Entrance Cap
	1	MM101	Light Duty Rack
KIT-100MH		MM505N	Flange c/w Neoprene Collar
	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MH200	Mast Coupler
		MM104	Entrance Cap
VIT 100MNE	1	MM140M	1-1/4 in. Male Reducer
KIT-100MNF		MM101	Light Duty Rack
	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
		MM105	1-1/2 in. Entrance Cap
	1	MM201	Heavy Duty Rack
KIT-150AM		MM505N	Flange c/w Neoprene Collar
	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM150M	1-1/2 in. Male Adaptor
		MM202	Entrance Cap
	1	MM201	Heavy Duty Rack
KIT-200AM	'	MM200M	2 in. Male Reducer
		MM505N	Flange c/w Neoprene Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolts
		MM202	Entrance Cap
	1	MM201	Heavy Duty Rack
KIT-200AMGR		MM200M	2 in. Male Reducer
KIT-ZUUAWUN		MM505N	Flange c/w Neoprene Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolts
	1	MM700	Service Mast Ground Clamp
		MM202	Entrance Cap
	1	MM201	Heavy Duty Rack
KIT-200MH		MM505N	Flange c/w Neoprene Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolts
	1	MH200	Mast Coupler

Cat. No.	Qty.	Consists of	Description
	1	MM104	Entrance Cap
		MM140M	1-1/4 in. Male Reducer
KIT-100HDM		MM201	Heavy Duty Rack
		MM503	Flange c/w Steel Collar
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolts
		SS401-E	Spool Rack
	1	E998J	2 in. Entrance Cap
	3	E997JC	2 in. Strap
	1	PH20	2 in. Hub PVC
KIT-200-PVC		E943J	2 in. Male Adaptor
	2	Cl1716	2 in. Locknut
		E986J	2 in. LB Type
	1	CIDUCT1	Duct Seal
		UA9AJCB-UPC	2 in. PVC Elbow
		MM202	2 in. Entrance Cap
		MM201	Spool Rack
	1	MM505N	Floor Flange
		MM200M	2 in. Male Reducer
	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
KIT-200AM-CP		E943J	2 in. Male Adaptor
	2	Cl1716	2 in. Locknut
		E986J	2 in. Entrance Cap
	1	DUCT SEAL	Duct Seal
		UA9AJCB-UPC	2 in. PVC Elbow
		MM202	2 in. Entrance Cap
		MM201	Spool Rack
	1	MM505N	Roof Flange
		MH200	2 in. Mast Coupler
VIT OCCUMUL OD	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
KIT-200MH-CP		E943J	2 in. Male Adaptor
	2	Cl1716	2 in. Locknut
	1	E986J	2 in. Entrance Cap
		CIDUCT1	Duct Seal
		UA9AJCB-UPC	2 in. PVC Elbow

### Mast Kits Suitable for Quebec and for all Regions

### KIT-200-PVC - Quebec



Cat. No.	Qty.	Consists of	Description			
This mast kit is used in conjunction with 2 in. rigid conduit						
	1	SS401-E	Spool Rack			
	I	E998J	2 in. Entrance Cap			
	3	E997JC	2 in. Strap			
	1	PH20	2 in. Hub PVC			
KIT-200-PVC	2	E943J	2 in. Male Adaptor			
-		CI1716	2 in. Locknut			
		E986J	2 in. LB Type			
	1	CIDUCT1	Duct Seal			
		UA9AJCB-UPC	2 in. PVC Elbow			

### KIT-200AM-CP - Quebec



Cat. No.	Qty.	Consists of	Description
This mast kit is used in o	onjunction with	n 2 in. rigid conduit	
		MM202	2 in. Entrance Cap
	4	MM201	Spool Rack
	ı	MM505N	Roof Flange
KIT-200AM-CP		MM200M	2 in. Male Reducer
	3	MM251	2 in. Pipe Strap (c/w Lag Screws)
	2	E943J	2 in. Male Adaptor
		Cl1716	2 in. Locknut
	1	E986J	2 in. Entrance Cap
		CIDUCT1	Duct Seal
		UA9AJCB-UPC	2 in. PVC Elbow

### KIT-200MH-CP - Quebec



Cat. No.	Qty.	<b>Consists of</b>	Description
	1	MM202	2 in. Entrance Cap
	1	MM201	Spool Rack
	1	MM505N	Roof Flange
	1	MH200	2 in. Mast Coupler
KIT-200MH-CP	3	MM251	2 in. Pipe Strap c/w Lag Screws 3/8 x 4 in.
KIT-ZUUWIN-GP	2	E943J	2 in. Male Adaptor
	2	Cl1716	2 in. Locknut
	1	E986J	2 in. Entrance Cap
	1	CIDUCT1	Duct Seal
	1	UA9AJCB-UPC	2 in. PVC Elbow

### KIT-400MH - For all Regions



Cat. No.	Qty.	Consists of	Description
This mast kit is used in	conjunction with	in. rigid conduit	
	1	CIEFA-4	4 in. Entrance Head
KIT-400MH	1	MM801	Heavy Duty Spool Rack
	1	MM806N	Roof Flange
	1	MH40	4 in. Mast Coupler
	3	Cl1532	Pipe Strap c/w Lag Screws (6) 3/8 x 5 in.

# Mast Kits Suitable for New Brunswick, Nova Scotia, Newfoundland and Prince Edward Island

#### **New Brunswick**

Cat. No.	Qty.	Consists of	Description
	1	MM104	Entrance Cap
KIT-100	1	MM140M	1-1/4 in. Male Reducer
KII-100	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar
	1	MM104	Entrance Cap
KIT-100NBMH	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
KI I-TUUNDIVIN	1	MH200	Mast Coupler
	1	MM505N	Flange c/w Neoprene Collar
	1	MM202	Entrance Cap
KIT-200	1	MM200M	2 in. Male Reducer
K11-200	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar
	1	MM202	Entrance Cap
	1	MM201	Heavy Duty Spool Rack
KIT-200MH	1	MH200	Mast Coupler
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar
	1	MM202	Entrance Cap
KIT-206NBMH	1	MH200	Mast Coupler
KI I-ZUUNDIVIN	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM506N	All Neoprene Roof Flange
	1	MM202	Entrance Cap
KIT-200NBMH	1	MH200	Mast Coupler
KI I-ZUUNDIVIN	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar
	1	MM104	Entrance Cap
KIT-106NBMH	1	MM506N	All Neoprene Roof Flange
VI I - I OOMDINU	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MH200	Mast Coupler

### **Newfoundland**

Cat. No.	Qty.	Consists of	Description
	1	MH200	Mast Coupler
	1	MM104	Entrance Cap
KIT-100MH	1	MM101	Light Duty Spool Rack
	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar
KIT-100NBMH	1	MM104	Entrance Cap
	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
KI I-TUUNDIVIN	1	MH200	Mast Coupler
	1	MM505N	Flange c/w Neoprene Collar
	1	MM202	Entrance Cap
KIT-205LDMH	1	MM101	Light Duty Spool Rack
	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MH200	Mast Coupler
	1	MM505N	Flange c/w Neoprene Collar

### **Nova Scotia**

Cat. No.	Qty.	Consists of	Description
	1	MM104	Entrance Cap
KIT-100MN	1	MM140M	1-1/4 in. Male Reducer
	1	MM101	Light Duty Spool Rack
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar
	1	MM104	Entrance Cap
KIT-100	1	MM140M	1-1/4 in. Male Reducer
K11-100	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar
	1	MM104	Entrance Cap
KIT-100NSMH	4	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
KII-IUUNSIVIN	1	MM505N	Flange c/w Neoprene Collar
	1	MH200	Mast Coupler
	1	MM202	Entrance Cap
	1	MM201	Heavy Duty Spool Rack
KIT-200AM	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolts
	1	MM200M	2 in. Male Reducer
	1	MM505N	Flange c/w Neoprene Collar
	1	MM202	Entrance Cap
KIT-200	1	MM200M	2 in. Male Reducer
K11-200	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar
	1	MM202	Entrance Cap
KIT-200NSMH	1	MH200	Mast Coupler
KI I-ZUUNSIVIN	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar

#### **Prince Edward Island**

Cat. No.	Qty.	<b>Consists of</b>	Description
	1	MM104	Entrance Cap
	1	MM101	Light Duty Spool Rack
KIT-100MH	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar
	1	MH200	Mast Coupler
	1	MM104	Entrance Cap
KIT-106NBMH	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
KIT-TOONDIVIN	1	MH200	Mast Coupler
	1	MM506N	All Neoprene Roof Flange
	1	MM202	Entrance Cap
	1	MM201	Heavy Duty Spool Rack
KIT-200MH	1	MH200	Mast Coupler
	3	MM255	Strap c/w 3/8 in. x 5 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar
	1	MM202	Entrance Cap
KIT-200NBMH	1	MH200	Mast Coupler
KI I-ZUUNDIVIT	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM505N	Flange c/w Neoprene Collar
	1	MM202	Entrance Cap
KIT-206NBMH	1	MH200	Mast Coupler
KI I-ZUUNDIVIII	3	MM251	Strap c/w 3/8 in. x 4 in. Lag Bolts
	1	MM506N	All Neoprene Roof Flange