


BE1 Series

100 A 600 V; King Size


Product Specifications

- Conductor range: 6-1/0 AWG
- Aluminum tunnel type connectors for both load and line sides
- For overhead, underground and combination overhead/underground
- · Supplied with screw type ring
- · Weatherproof Type 3R enclosure
- · Primarily used in all provinces

Note: Supply from an underground network often requires use of stud type connector. Consult your local utility.



GROUND BOTTOM



Cat. No.	Description	Di	Dimensions (in.)			Weight Each	
		Н	W	D	lb.	kg	
4 JAW							
BE1-V	Overhead, hub opening		8-1/4	4-3/8	8	3.6	
BE1-1 1/4V	Overhead, hub opening, c/w 1-1/4 in. hub						
BE1-1 1/2V	Overhead, hub opening, c/w 1-1/2 in. hub						
BE1-TV	Underground	14-5/8					
BE1-TCV	Combination overhead-underground						
BE11-V-CM	Overhead, twin hub opening						
BE11-1 1/4V	Overhead, twin hub opening c/w 1-1/4 in. hubs						
FACTORY-INSTAL	LED ACCESSORIES						
Include: -5	5th jaw, standard capacity, 9 o'clock position						
-9	5 th jaw, full capacity, 9 o'clock position						
-6	5th jaw, full capacity, 6 o'clock position						
-IN	Insulated neutral						
-W	Water heater lugs						