

LED Lamps

02

The perfect replacement for traditional lamps, E-Lume LED lamps offer good value with great performance while providing bright clean light and consistent colour from lamp to lamp.



Order code	Description	Watts (W)	Base	Volts (VAC)	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (inner/master)
MR16												
63605	LED/MR16/7W/30K/25/ELUME	7	GU5.3	12	3 000	80	40 000	520	25	2 000	50	12/48
63606	LED/MR16/7W/30K/40/ELUME	7	GU5.3	12	3 000	80	40 000	520	40	1 100	50	12/48
MR16 - E26												
64542	LED/MR16E26/7W/40K/35/ELUME	7	E26	120	4 000	80	30 000	525	35	1 150	50	6/48
GU10												
64634	LED/GU10/7W/30K/25/ELUME	7	GU10	120	3 000	84	25 000	563	25	2 450	50	6/48
64635	LED/GU10/7W/30K/25/GRY/ELUME	7	GU10	120	3 000	84	25 000	563	25	2 450	50	6/48
GU10 - All Glass												
65394	LED/GU10/5W/30K/40/GLASS/ELUME	5	GU10	120	3 000	82	25 000	544	40	967	50	10/100
65400	LED/GU10/5W/40K/40/GLASS/ELUME	5	GU10	120	4 000	83	25 000	538	40	965	50	10/100

Lumen values are derived from photometric testing. For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com



LED PAR Lamps

02

With an aluminum heat sink and a quality glass lens, this LED lamp looks just like a traditional halogen PAR. Entirely dimmable, it allows you to create any desired mood.



Order code	Description	Watts (W)	Base	Volts (VAC)	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (master)
PAR20												
64904	LED/P20/S2/7W/30K/25D/ELUME	7	E26	120	3 000	≥80	25 000	544	25	1 200	50	20
64905	LED/P20/S2/7W/30K/40D/ELUME	7	E26	120	3 000	≥80	25 000	575	40	600	50	20
64912	LED/P20/S2/7W/40K/40D/ELUME	7	E26	120	4 000	≥80	25 000	558	40	650	50	20
PAR30SN												
64906	LED/P30S/S2/10W/30K/25D/ELUME	10	E26	120	3 000	≥80	25 000	948	25	2 150	60	15
64907	LED/P30S/S2/10W/30K/40D/ELUME	10	E26	120	3 000	≥80	25 000	879	40	1 000	60	15
64913	LED/P30S/S2/10W/40K/40D/ELUME	10	E26	120	4 000	≥80	25 000	889	40	1 020	60	15
PAR30LN												
64908	LED/P30L/S2/10W/30K/25D/ELUME	10	E26	120	3 000	≥80	25 000	891	25	2 150	60	15
64909	LED/P30L/S2/10W/30K/40D/ELUME	10	E26	120	3 000	≥80	25 000	852	40	1 000	60	15
64914	LED/P30L/S2/10W/40K/40D/ELUME	10	E26	120	4 000	≥80	25 000	833	40	1 020	60	15
PAR38												
64910	LED/P38/S2/15W/30K/40D/ELUME	15	E26	120	3 000	≥80	25 000	1 226	40	1 550	90	15
64911	LED/P38/S2/15W/40K/40D/ELUME	15	E26	120	4 000	≥80	25 000	1 325	40	1 600	90	15



Lumen values are derived from photometric testing. For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com

LED ICE PAR Lamps

The ICE finish paired with a wide beam angle ensures a diffused light to eliminate dark zones and avoid hotspots.



Traditional finish ICE finish

02



PAR20



PAR30SN



PAR30LN



PAR38

Order code	Description	Watts (W)	Base	Volts (VAC)	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (master)
PAR20												
64900	LED/P20/ICE/7W/30K/FL/ELUME	7	E26	120	3 000	≥80	25 000	500	40	450	50	20
PAR30SN												
64901	LED/P30S/ICE/10W/30K/FL/ELUME	10	E26	120	3 000	≥80	25 000	750	40	880	60	15
PAR30LN												
64902	LED/P30L/ICE/10W/30K/FL/ELUME	10	E26	120	3 000	≥80	25 000	750	40	880	60	15
PAR38												
64903	LED/P38/ICE/15W/30K/FL/ELUME	15	E26	120	3 000	≥80	25 000	1 100	40	1 150	90	15

Lumen values are derived from photometric testing. For a complete list of compatible dimmers, please visit www.standardpro.com

