

ECONOMY SERIES

A quality fan for an incredible value. Torsion spring grille mounting means no tools are required. The compact housing fits easily between wall studs and features double strength flanges with keyholes for fast installation. Ceiling or wall application. HVI certified.



Part No.	Description	CFM @ 0.1" SP	Sones @ 0.1" SP	Duct	Housing	Weight (lb.)	Std. Pack	UPC
EC50	Economy fan	50	3.0	3"	8 1/16" x 7 3/8" x 3 7/8"	3.6	1 pc.	055321600255
EC70	Economy fan	70	5.5	3"	8 1/16" x 7 3/8" x 3 7/8"	4.1	1 pc.	055321600262
Project Packs								
ECF50	Economy project finish pack, contains 6 motor assemblies and 6 grilles.	50	3.0	N/A	N/A	2.1	6 pcs.	50055321600274
ECF70	Economy project finish pack, contains 6 motor assemblies and 6 grilles.	70	5.5	N/A	N/A	2.5	6 pcs.	50055321600281
ECH600	Project housing pack for above finish packs. Contains 6 housings and 6 duct connectors.	N/A	N/A	3"	8 1/16" x 7 3/8" x 3 7/8"	1.6	6 pcs.	50055321600298

COMBINATION UNITS - HEATER, FAN, LIGHT

Multi-functional providing heat, ventilation and light. HVI certified (except 161M).



Part No.	Description	CFM @ 0.1" SP	Sones @ 0.1" SP	Duct	Housing	Weight (lb.)	Std. Pack	UPC
161M	One-bulb heater - no fan	N/A	N/A	N/A	8 3/8" x 8 1/8" x 6"	5.0	1 pc.	055321620581
162M	One-bulb heater - with fan	70	3.5	4"	8 3/8" x 8 1/8" x 6 3/8"	6.9	1 pc.	055321620574
164	Two-bulb heater - with fan	70	3.5	4"	14 1/4" x 8 3/8" x 6 3/8"	16.0	1 pc.	055321620161
655C	Heater/fan light - designer styled white polymeric grille, 100-watt light capacity and 1,300-watt heater	70	4.0	4"	14 1/4" x 8 1/4" x 5 3/4"	14.0	1 pc.	026715156245

RECESSED FAN/LIGHT

The recessed fan/light is at home in any room of the house where you'd like to keep the air fresh and comfortable. Two distinct functions in one clever design.



Part No.	Description	CFM @ 0.1" SP	Sones @ 0.1" SP	Duct	Housing	Weight (lb.)	Std. Pack	UPC
744C	Recessed fan light with 6" white trim	70	1.5	4"	12 3/4" x 8 1/4" x 6 3/4"	9.8	1 pc.	026715165704