



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

AYP750  
 7818107377811  
 700/750 AL HYPLUG  
 Active

**Web Use**  
 BURNDY Product Line

B Length (Fraction)  
 B Length (in)  
 Strip Length  
 Pin Length (in)

**Dimensional**

1-5/8  
 1.59  
 1-3/4  
 1.76

**General**

Product Description

Aluminum Compression Pin  
 Adapter, 700/750 kcmil, 0.81 "  
 Plug Dia, 1.76" Plug Length, Al/Cu  
 Rated, Tin Plated

**Conductor(s)**

Aluminum Size (Range)  
 Copper Stranded (Range)

700 kcmil-750 kcmil  
 700 kcmil-750 kcmil

**Physical**

Type of Plating  
 Insulation Type  
 Pin Type  
 Plated (Yes or No)  
 Index Number  
 Product Material  
 Insulated (Yes or No)

Tin  
 Rubber  
 Straight  
 Y  
 936  
 Aluminum  
 Y

**Approvals / Certifications**

UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS  
 Industry Standards

Y  
 Y  
 Compliant  
 N  
 N  
 UL468A-468B

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175