



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

BG12  
7818108070644  
1X BRAID 12 1.50 C-C 41  
Active

**Web Use**  
BURNDY Product Line

Length (in)  
E - in  
Hole Size (in)

**Dimensional**  
12.00  
1.50  
0.44

Outdoor Amperage Rating (approximate)  
Indoor Amperage Rating (approximate)

**Electrical**  
495  
415  
**Approvals / Certifications**

UL Listed  
CSA Certified  
ROHS Compatible  
UL Recognized  
CULUS  
Industry Standards

Y  
N  
Compliant  
N  
N  
UL467

Connector Type  
Plated (Yes or No)  
Product Material

**Physical**  
Braid  
Y  
Copper

Number of Braids (Ferrule)

**General**  
1  
Copper Braid, 12" Long, 1 Braid, 2 Holes 2 Ferrules, 7/16" Stud, 1-1/2" Stud Hole Spacing, 415 amps Indoor, 495 amps Outdoor

Product Description

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175