



BURNDY Catalog Number
UPC Number
Description
Status

BITO350
 7818101559366
 350-10, 2 SIDE, UNI-TAP
 Active

Web Use
 BURNDY Product Line

Width (in)
 Hex Size (Key)
 Length (in)
 Height (in)

Dimensional
 3.00
 5/16
 2.22
 2.50

Min Voltage Rating

Electrical
 600

Number of Ports
 Number of Screws

General
 2
 2

Product Description

Aluminum Multiple Tap
 Connector, Clear Insulated, 2 Port,
 2 Sided Entry, 10 AWG-350 kcmil

Aluminum Size (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)

Conductor(s)
 8 AWG-350 kcmil
 N/A
 10 AWG-350 kcmil

Type of Hardware
 Type of Plating
 Insulation Type
 Plated (Yes or No)
 Product Material

Physical
 Aluminum
 Unplated
 Plastisol
 N
 Aluminum

Rated for Direct Burial
 UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Approvals / Certifications
 N
 Y
 Y
 Compliant
 N
 N
 UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175