



BURNDY Catalog Number GAR3905BU
UPC Number 7818100015233
Description 4-4/0, 4-5 IPS
Status Active

Web Use
 BURNDY Product Line

Dimensional
 Width (in) 7.50
 Length (in) 1.75
 Height (in) 7.50
 Size (Hex) or Size (Bolt) 3/8
 Size (Hex) or Size (Bolt) - in 0.38
 B Length (in) 1.75

Product Description

General
 Mechanical Grounding Connector,
 Conductor to Water Pipe, 4-4/0
 AWG, 4"-5" Pipe, 3/8" Stud

Type of U Bolt

Other
 422

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards
Rated for Direct Burial

Approvals / Certifications
 Y
 Y
 Compliant
 N
 N
 UL467
 Y

Copper Tube Size (SCH40) - Range 4-5
Rod Size (Range) N/A
Copper Solid Size (Range) N/A
Copper Stranded (Range) 4-4/0
Rebar Size (Range) N/A

Conductor(s)

Type of Hardware DURIUM® Silicon Bronze
Installation Torque 200
Type of Plating Unplated
Plated (Yes or No) N
Product Material Copper Alloy

Physical

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175