



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

K11A30U  
 7818103702611  
 TWO:6 STR-300 DUAL RATED  
 Active

**Web Use**  
 BURNDY Product Line

Dimensional	
Width (in)	1.00
Length (in)	3.00
Height (in)	2.03
Thickness	0.50
D - in	0.94
Stud Size (Fraction)	5/16
N (in)	0.47
General	
Number of Conductors	2
Number of Holes	2
Product Description	Aluminum Universal Terminal, 1 Hole, Two: 6 AWG (Str)-300 kcmil, 5/16" Stud, 2 Screws, Al/Cu Rated, Tin Plated
Conductor(s)	
Aluminum Size (Range)	6 AWG-300 kcmil
Copper Solid Size (Range)	4 AWG-4/0 AWG
Copper Stranded (Range)	6 AWG-300 kcmil
Physical	
Installation Torque	275
Type of Plating	Tin
Connector Type	Terminal
Plated (Yes or No)	Y
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B
<b>Documentation</b>	

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175