



BURNDY Catalog Number
UPC Number
Description
Status

K2A40U
 7818106002522
 TWO:300-800 DUAL RATED
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in)	3.19
Length (in)	3.38
Bolt Hole Size (in)	0.63
Thickness	0.50
D - in	1.66
Pad Width (in)	3.20
N (in)	0.88

General

Number of Conductors	2
Number of Holes	1
Product Description	Aluminum Universal Terminal, 2 Conductor, 1 Hole, 300-800 kcmil, 5/8" Stud, 2 Screws, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range)	300 - 800 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	300 kcmil-800 kcmil

Physical

Installation Torque	500
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	5/8
Plated (Yes or No)	N
Product Material	Aluminum

Approvals / Certifications

Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175