



BURNDY Catalog Number
UPC Number
Description
Status

K2C26
 7818102574011
 2-2/0 STR 17/32 POST 2 C
 Active

Web Use
 BURNDY Product Line

Dimensional

Stud Length (in)	17/32,0.52
Thread Size	1/2-13
Height (in)	1.38
D or Diameter (Fraction) (in)	3/4
Nut Width (Fraction)	1
Nut Width (in)	1.04
D - in	0.75
Body Width (Fraction)	7/8
Body Width (in)	0.88
Height (Fraction) (in)	1-3/8

General

Product Description
 Mechanical Grounding Connector, Cable to Flat, 2-2/0 AWG (Str) / 2-3/0 AWG (Sol), 1/2" Stud, Body height:1.81

Conductor(s)

Copper Solid Size (Range)	2 AWG-3/0 AWG
Copper Stranded (Range)	2 AWG-2/0 AWG

Physical

Type of Plating	Unplated
Plated (Yes or No)	N
Product Material	Leaded Bronze Alloy

Approvals / Certifications

Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175