



BURNDY Catalog Number
UPC Number
Description
Status

KSU31
 7818100370033
 SERVIT UNIV 4/0-350
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 1.36
 Cross Flats 1.69

General

Product Description

Tin-plated, high strength copper alloy SERVIT[®] with spacer. Spacer separates dissimilar conductors and provides long contact length that prevents high pressure point contacts between run and tap conductors.

Conductor(s)

Copper Tap Range 4 AWG-350 kcmil
 CopperWeld Solid Run Size (Range) N/A
 Copper Stranded Run (Range) 4/0 AWG-350 kcmil
 CopperWeld Stranded Tap Size (Range) N/A
 Copper Solid Tap (Range) N/A
 CopperWeld Solid Tap Size (Range) N/A
 Copper Solid Run Size (Range) N/A
 CopperWeld Stranded Run Size (Range) N/A

Physical

Installation Torque 650
 Type of Plating Tin - Electro Plated
 Connector Type Split Bolt
 Plated (Yes or No) Y
 Product Material Copper

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Exempt
 UL Recognized N
 CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175