



BURNDY Catalog Number
UPC Number
Description
Status

QA28B
 7818103147600
 3/0-4/0 CU LUG 1 BLT 1 H
 Active

Web Use
 BURNDY Product Line

Dimensional

Height (Fraction) (in)	1-5/16
Length (in)	2.25
Thickness (in)	1/4
Height (in)	1.31
D or Diameter (Fraction) (in)	1-1/16
Hole Size (Fraction)	13/32
Stud Size (in)	3/8
Thickness	0.25
D - in	1.06
Pad Width (in)	1.00
N (Fraction)	17/32
N (in)	0.53
Hole Size (in)	0.41
Length (Fraction)	2-1/4

General

Number of Holes	1
Product Description	Copper Terminal, Heavy Duty, 1 Hole, 3/0-4/0 AWG (Str), 3/8" Stud, 1 Screw

Conductor(s)

Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	150 (61) Navy-200 (61) Navy
Copper Stranded (Range)	3/0 AWG-4/0 AWG

Physical

Installation Torque	250
Type of Plating	Unplated
Connector Type	Terminal
Plated (Yes or No)	N
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	N
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175