



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

QP10F25X03D  
 7818102935777  
 FEM DISC-12-10AWG-VINYL  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Tab Size .250 X .032  
 Strip Length 3/8"  
 Width (in) 0.29  
 Length (in) 0.98  
 F - Spacing (in) (Width - Center to Center) 0.13  
 B Length (in) 0.25

**General**

**Product Description** Brass Female Quick Disconnect, 10-12 AWG, Vinyl Insulated, Tin Plated

**Other**

**Bulk Package** QP10F25X03B

**Approvals / Certifications**

UL Listed N  
 CSA Certified N  
 ROHS Compatible Compliant  
 UL Recognized N  
 CULUS Y  
 Industry Standards UL467

**Conductor(s)**

Copper Solid Size (Range) N/A  
 Copper Stranded (Range) 12 AWG-10 AWG

**Physical**

Type of Plating Tin  
 Connector Type Female Disconnect  
 Insulation Type Vinyl  
 Plated (Yes or No) Y

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175