



BURNDY Catalog Number
UPC Number
Description
Status

TP108F
 7818107106855
 FORK- 12- 10 AWG- VINYL
 Active

Web Use
 BURNDY Product Line

Dimensional	
Strip Length	19/64
Length (in)	0.98
Tongue Type	Fork
Thickness	0.04
B Length (in)	0.34
Pad Width (in)	0.31
Electrical	
Max Voltage Rating	600
General	
Product Description	Insulated Brazed Fork Terminal, Insulated Brazed Fork Terminal, Smooth Entry, #12-#10, 600V, #6-#8 Stud, Vinyl Insulated, Tin Plated
Other	
Bulk Package	BA10EF8
Physical	
Type of Plating	Tin
Connector Type	Terminal - Fork
Insulation Type	Vinyl
Plated (Yes or No)	Y
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	12 AWG-10 AWG
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175