



BURNDY Catalog Number YA262N
UPC Number 7818105028088
Description 2/0 CU 2-HOLE LONG 1/2
Status Active

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	4.97
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.52
Barrel Type	Long
Thickness	0.12
B Length (in)	1.50
Pad Width (in)	0.83
E - in	1.75
Strip Length	1-9/16
General	
Number of Holes	2
Product Description	Copper Compression lug, 2 Hole w/o Inspection Window, 2/0 AWG, 1/2" stud, 1-3/4" Stud Hole Spacing, long barrel, Tin Plated
Conductor(s)	
Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	2/0 AWG
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Black
Plated (Yes or No)	Y
Index Number	13
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175