



BURNDY Catalog Number YA29LNT38
UPC Number 7818100185455
Description 250,SHORT,3/8,NAR.TONG
Status Active

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	2.96
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.16
B Length (in)	1.06
Pad Width (in)	0.96
Strip Length	1-1/8
General	
Number of Holes	1
Product Description	Copper Compression lug, Narrow Tongue, 1 Hole w/ Inspection Window, 250 kcmil, 3/8" Stud, Short Barrel, Tin Plated
Conductor(s)	
Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	250 kcmil
Physical	
Type of Plating	Tin - Electro Plated
Color Code	Yellow
Plated (Yes or No)	Y
Index Number	16
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175