



BURNDY Catalog Number
UPC Number
Description
Status

YA392N
 7818105223566
 750 CU 2-HOLE LONG NEMA
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	6.87
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.52
Barrel Type	Long
Thickness	0.27
B Length (in)	2.88
Pad Width (in)	1.91
E - in	1.75
Strip Length	2-15/16

General

Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/o Inspection Window, 750 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Long Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	750 kcmil

Physical

Type of Plating	Tin
Bolt Hole Size	1/2
Color Code	Black
Plated (Yes or No)	Y
Index Number	24
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175