

YAL262T38 : CANLG-2/0STR-
SHORT-3/8 X1



Experience. Technology. Answers.™

www.burndy.com

BURNDY® PRODUCTS

Specifications

Dimensional

Tongue Angle	Straight
Length (in)	2.74
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.13
B Length (in)	0.73
Pad Width (in)	0.83
E - in	1

Other Features

UPC	78181041697
-----	-------------

General

Number of Holes	2
-----------------	---

Conductor(s)

Copper Solid Size (Range)	2/0
Copper Stranded (Range)	2/0

Physical

Type of Plating	Tin - Electro Plated
Color Code	Black
Plated (Yes or No)	Y
Index Number	13
Product Material	Copper

Approvals / Certifications

Industry Standards	UL468A -468B
UL Listed	Yes Y
CSA Certified	Yes Y
ROHS Compatible	Compliant
UL Recognized	N