

YAL4CT516 : CANLUG-#4 STR-
SHORT-5/16



Experience. Technology. Answers.™

www.burndy.com

BURNDY® PRODUCTS

Specifications

Dimensional	
Tongue Angle	Straight
Length (in)	1.79
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.33
Barrel Type	Standard
Thickness	0.08
B Length (in)	0.73
Pad Width (in)	0.58
Other Features	
UPC	78181041754
General	
Number of Holes	1
Conductor(s)	
Copper Stranded (Range)	4
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	5/16
Color Code	Gray
Plated (Yes or No)	Y
Index Number	8
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A-468B
UL Listed	Yes Y
CSA Certified	Yes Y
ROHS Compatible	Compliant
UL Recognized	N